

NA2XS(FL)2Y

, PE ()
 가 VDE 0276-620 PE , ,

NA2XS(FL)2Y

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
 With aluminium conductor



EVU

HD 620/VDE 0276-620 10-C (4)
 0.6m, 0.8m

가 :

PE
 HD 620/VDE 0276-620, 10-C, 7
 +20 °C)
 가 +30 °C) : VDE 0298-4, VDE 0298-4
 . (T12)

, (HD 620/VDE 0276-620, Part 10-C, 5
 8 (HD 620/VDE 0276-620, Part 10-C, point 5 ,
 /

(24.04.2024)

NA2XS(FL)2Y

HD 620/ VDE 0276-620

"rm": r = , m =
: 가 (XLPE)

PE : PE, 가

ETIM 5:	ETIM 5.0 Class-ID: EC001140
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001140
	ETIM 6.0 Class :
:	
:	: 15 x
:	U ₀ /U: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
:	6/10 kV: 15 kV, 12/20 kV: 30 kV, 18/30
:	kV: 45 kV
:	: -40°C ~ +70°C
	: -40°C ~ +90°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths

가 VAT 가 가 .

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
6/10 (12) kV				
38107624	1 x 120 RM/16	31	182	951
38107625	1 x 150 RM/25	32	283	1134
38107626	1 x 240 RM/25	36	283	1473
38107627	1 x 400 RM/35	41	394	2091
12/20 (24) kV				
38107628	1 x 70 RM/16	32	182	914
38107629	1 x 70 RM/25	32	283	1015
38107630	1 x 95 RM/25	34	283	1100
38107631	1 x 120 RM/16	35	182	1136
38106494	1 x 150 RM/25	36	283	1327
38107252	1 x 185 RM/25	38	283	1474
38107253	1 x 240 RM/25	40	283	1691
38107632	1 x 300 RM/25	42	283	1914
38106656	1 x 400 RM/35	45	394	2298
38107633	1 x 500 RM/35	48	394	2675
18/30 (36) kV				
38107634	1 x 70 RM/16	37	182	1144
38107635	1 x 95 RM/16	38	182	1273
38107636	1 x 120 RM/16	40	182	1389
38107637	1 x 150 RM/25	41	283	1590
38106590	1 x 185 RM/25	43	283	1750
38107638	1 x 240 RM/25	45	283	1984
38107639	1 x 300 RM/25	48	283	2225
38107640	1 x 400 RM/35	50	394	2629
38107641	1 x 500 RM/35	53	394	3042