

HITRONIC® POF DUPLEX BUFFERED FIBRES

PE

HITRONIC® POF DUPLEX PE, PE POF , J-V2Y 2x1P980/1000



70 m

EMC

(POF)

PE

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

HITRONIC® POF DUPLEX BUFFERED FIBRES

:

ETIM 5:

ETIM 5.0 Class-ID: EC000034

ETIM 5.0 Class-Description:

ETIM 6:

ETIM 6.0 Class-ID: EC000034

ETIM 6.0 Class : LWL

:

2x2.2mm

:

Black/black with white dots

Fibre type:

POF - P980/1000

::

J-V2Y

:

: PMMA

가 :

10 x

가 :

: 10 N

- : 30 N

:

: -55 ~ +85°C

: -10°C +50°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths

가 VAT 가 가 .

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



HITRONIC® POF DUPLEX BUFFERED FIBRES

		Fibre type	Number of fibres	(mm)	(kg/km)
28000002	HITRONIC® POF DUPLEX PE	980/1000 POF	2	4.4	7.6

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16