

H05Z-K 90°C

Harmonised,

H05Z-K 90°C, HAR,

300 / 500V

CPR: www.lappkabel.com/cpr

(HAR)

ÖLFLEX® HEAT 125 SC



가 가 가

ÖLFLEX® HEAT 125 SC

가

가
IEC 61034 ,
: IEC 60332-1-2

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

H05Z-K 90°C

<HAR>EN 50525-3-41

가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

VDE 0295 5/ IEC 60228 5

가 가

:

EN 50565-1
4 x (OD), 2 x OD

:

U0/U: 300/500 V

:

2000 V AC

:

VDE 0298-4

EN 50565-1/ VDE 0298-565-1

:

: -5°C ~ +90°C

: -40°C ~ +90°C

가

가

(.)

가

: ≤ 30 kg,

,

가

VAT

가

가

.

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

H05Z-K 90°C

	(mm²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4725001S	0.5	2.1 - 2.6	/	-	-	250	4.8	9
4725121S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725031S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725011S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725061S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725021S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725141S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725091S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725071S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725111S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725051S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725041S	0.5	2.1 - 2.6		-	-	250	4.8	9
4725002S	0.75	2.2 - 2.8	/	-	-	250	7.2	11
4725122S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725032S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725012S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725062S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725022S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725142S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725092S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725072S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725112S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725052S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725042S	0.75	2.2 - 2.8		-	-	250	7.2	11
4725003S	1	2.4 - 2.9	/	-	-	250	9.6	14
4725123S	1	2.4 - 2.9		-	-	250	9.6	14
4725033S	1	2.4 - 2.9		-	-	250	9.6	14
4725013S	1	2.4 - 2.9		-	-	250	9.6	14
4725063S	1	2.4 - 2.9		-	-	250	9.6	14
4725023S	1	2.4 - 2.9		-	-	250	9.6	14
4725143S	1	2.4 - 2.9		-	-	250	9.6	14
4725093S	1	2.4 - 2.9		-	-	250	9.6	14
4725073S	1	2.4 - 2.9		-	-	250	9.6	14
4725113S	1	2.4 - 2.9		-	-	250	9.6	14

H05Z-K 90°C

	(mm²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4725053S	1	2.4 - 2.9		-	-	250	9.6	14
4725043S	1	2.4 - 2.9		-	-	250	9.6	14
4725001	0.5	2.1 - 2.6	/	100	-	-	4.8	9
4725001K	0.5	2.1 - 2.6	/	-	3000	-	4.8	9
4725121	0.5	2.1 - 2.6		100	-	-	4.8	9
4725121K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725031	0.5	2.1 - 2.6		100	-	-	4.8	9
4725031K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725011	0.5	2.1 - 2.6		100	-	-	4.8	9
4725011K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725061	0.5	2.1 - 2.6		100	-	-	4.8	9
4725061K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725021	0.5	2.1 - 2.6		100	-	-	4.8	9
4725021K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725141	0.5	2.1 - 2.6		100	-	-	4.8	9
4725141K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725091	0.5	2.1 - 2.6		100	-	-	4.8	9
4725091K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725071	0.5	2.1 - 2.6		100	-	-	4.8	9
4725071K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725111	0.5	2.1 - 2.6		100	-	-	4.8	9
4725111K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725051	0.5	2.1 - 2.6		100	-	-	4.8	9
4725051K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725041	0.5	2.1 - 2.6		100	-	-	4.8	9
4725041K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725081	0.5	2.1 - 2.6		100	-	-	4.8	9
4725081K	0.5	2.1 - 2.6		-	3000	-	4.8	9
4725002	0.75	2.2 - 2.8	/	100	-	-	7.2	11
4725002K	0.75	2.2 - 2.8	/	-	2500	-	7.2	11
4725122	0.75	2.2 - 2.8		100	-	-	7.2	11
4725122K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725032	0.75	2.2 - 2.8		100	-	-	7.2	11
4725032K	0.75	2.2 - 2.8		-	2500	-	7.2	11

H05Z-K 90°C

	(mm²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4725012	0.75	2.2 - 2.8		100	-	-	7.2	11
4725012K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725062	0.75	2.2 - 2.8		100	-	-	7.2	11
4725062K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725022	0.75	2.2 - 2.8		100	-	-	7.2	11
4725022K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725142	0.75	2.2 - 2.8		100	-	-	7.2	11
4725142K	0.75	2.1 - 2.8		-	2500	-	7.2	11
4725092	0.75	2.1 - 2.8		100	-	-	7.2	11
4725092K	0.75	2.1 - 2.8		-	2500	-	7.2	11
4725072	0.75	2.2 - 2.8		100	-	-	7.2	11
4725072K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725112	0.75	2.2 - 2.8		100	-	-	7.2	11
4725112K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725052	0.75	2.2 - 2.8		100	-	-	7.2	11
4725052K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725042	0.75	2.2 - 2.8		100	-	-	7.2	11
4725042K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725082	0.75	2.2 - 2.8		100	-	-	7.2	11
4725082K	0.75	2.2 - 2.8		-	2500	-	7.2	11
4725003	1	2.4 - 2.9	/	100	-	-	9.6	14
4725003K	1	2.4 - 2.9	/	-	2000	-	9.6	14
4725123	1	2.4 - 2.9		100	-	-	9.6	14
4725123K	1	2.4 - 2.9		-	2000	-	9.6	14
4725033	1	2.4 - 2.9		100	-	-	9.6	14
4725033K	1	2.4 - 2.9		-	2000	-	9.6	14
4725013	1	2.4 - 2.9		100	-	-	9.6	14
4725013K	1	2.4 - 2.9		-	2000	-	9.6	14
4725063	1	2.4 - 2.9		100	-	-	9.6	14
4725063K	1	2.4 - 2.9		-	2000	-	9.6	14
4725023	1	2.4 - 2.9		100	-	-	9.6	14
4725023K	1	2.4 - 2.9		-	2000	-	9.6	14
4725143	1	2.4 - 2.9		100	-	-	9.6	14
4725143K	1	2.4 - 2.9		-	2000	-	9.6	14

H05Z-K 90°C

		(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4725093	1		2.4 - 2.9		100	-	-	9.6	14
4725093K	1		2.4 - 2.9		-	2000	-	9.6	14
4725073	1		2.4 - 2.9		100	-	-	9.6	14
4725073K	1		2.4 - 2.9		-	2000	-	9.6	14
4725113	1		2.4 - 2.9		100	-	-	9.6	14
4725113K	1		2.4 - 2.9		-	2000	-	9.6	14
4725053	1		2.4 - 2.9		100	-	-	9.6	14
4725053K	1		2.4 - 2.9		-	2000	-	9.6	14
4725043	1		2.4 - 2.9		100	-	-	9.6	14
4725043K	1		2.4 - 2.9		-	2000	-	9.6	14
4725083	1		2.4 - 2.9		100	-	-	9.6	14
4725083K	1		2.4 - 2.9		-	2000	-	9.6	14
4725263K	1		2.4 - 2.9	/	-	2000	-	9.6	14



H05Z-K 90°C



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16