

# H05Z1-K

Harmonised,

H05Z1-K, , +70°C , , 300/500V

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)

(HAR), +70°C  
H05Z-K 90°C



가 가 가

H05Z-K 90°C

가

가  
IEC 61034 , /  
: IEC 60332-1-2

EN 50525-3-31/VDE 0285-525-3-31 <HAR>

(30.04.2024)

# H05Z1-K

가

:

ETIM 5:

:

:

:

:

:

:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

VDE 0295 5/ IEC 60228 5

가 가

EN 50565-1

4 x (OD), 2 x OD

U0/U: 300/500 V

2000 V AC

VDE 0298-4

EN 50565-1/ VDE 0298-565-1

: +5°C ~ +70°C

: -40°C ~ +70°C

: 30 kg,

,

가 VAT 가 가 .

가 가 ( . ) 가 .



H05Z1-K

	(mm <sup>2</sup> )	(mm)		m/	(kg/km)	(kg/km)
4724053	0.75	2.2 - 2.7		100	7.2	11
4724055	1	2.4 - 2.8		100	9.6	14
4724058	1	2.4 - 2.8		100	9.6	14
4724057	1	2.4 - 2.8		100	9.6	14

(30.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16