


# H05V-K <HAR>

<HAR>

H05V-K, HAR, , PVC, 300/500V, , ,class 5 / , /

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)  
<HAR>



<HAR> 가 ( : <VDE><HAR> )  
. <HAR> 가 .

: IEC 60332-1-2  
: d1 = 18 mm; d2 = 200 mm; b = 85 mm

No cable type certified core insulation colour according to EN 50525-1/VDE 0285-525-1: transparent  
EN 50525-2-31 <HAR>

5(IEC 60228 ) 가 가  
: PVC

ETIM 5: ETIM 5.0 Class-ID: EC000993

# H05V-K <HAR>

ETIM 6:

:

:

:

:

:

:

ETIM 5.0 Class :

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

VDE 0295 5/ IEC 60228 5

가 가

EN 50565-1

4 x (OD), 2 x OD

U0/U: 300/500 V

2000 V

VDE 0298 4

EN 50565-1/ VDE 0298-565-1

: -40°C +70°C

, 가 가 . ( . ) 가 .

,

가 VAT 가 가 .

		(mm <sup>2</sup> )	(mm)	m/	m/	(kg/km)	(kg/km)
4510001	/	0.5	2.1 - 2.5	100	-	4.8	9
4510011		0.5	2.1 - 2.5	100	-	4.8	9
4510021		0.5	2.1 - 2.5	100	-	4.8	9
4510141		0.5	2.1 - 2.5	100	-	4.8	9
4510031		0.5	2.1 - 2.5	100	-	4.8	9
4510111		0.5	2.1 - 2.5	100	-	4.8	9
4510121		0.5	2.1 - 2.5	100	-	4.8	9
4510071		0.5	2.1 - 2.5	100	-	4.8	9
4510081		0.5	2.1 - 2.5	100	-	4.8	9
4510091		0.5	2.1 - 2.5	100	-	4.8	9
4510041		0.5	2.1 - 2.5	100	-	4.8	9
4510051		0.5	2.1 - 2.5	100	-	4.8	9
4510061		0.5	2.1 - 2.5	100	-	4.8	9
4510161		0.5	2.1 - 2.5	100	-	4.8	9
4510921	/	0.5	2.1 - 2.5	100	-	4.8	9
4510002	/	0.75	2.2 - 2.7	100	-	7.2	12
4510012		0.75	2.2 - 2.7	100	-	7.2	12
4510022		0.75	2.2 - 2.7	100	-	7.2	12
4510142		0.75	2.2 - 2.7	100	-	7.2	12
4510032		0.75	2.2 - 2.7	100	-	7.2	12
4510112		0.75	2.2 - 2.7	100	-	7.2	12
4510122		0.75	2.2 - 2.7	100	-	7.2	12
4510072		0.75	2.2 - 2.7	100	-	7.2	12
4510082		0.75	2.2 - 2.7	100	-	7.2	12
4510092		0.75	2.2 - 2.7	100	-	7.2	12
4510042		0.75	2.2 - 2.7	100	-	7.2	12
4510052		0.75	2.2 - 2.7	100	-	7.2	12
4510062		0.75	2.2 - 2.7	100	-	7.2	12
4510922	/	0.75	2.2 - 2.7	100	-	7.2	12
4510162		0.75	2.2 - 2.7	100	-	7.2	12
4510003	/	1	2.4 - 2.8	100	-	9.6	15
4510013		1	2.4 - 2.8	100	-	9.6	15
4510023		1	2.4 - 2.8	100	-	9.6	15
4510143		1	2.4 - 2.8	100	-	9.6	15

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

		(mm <sup>2</sup> )	(mm)	m/	m/	(kg/km)	(kg/km)
4510033		1	2.4 - 2.8	100	-	9.6	15
4510113		1	2.4 - 2.8	100	-	9.6	15
4510123		1	2.4 - 2.8	100	-	9.6	15
4510073		1	2.4 - 2.8	100	-	9.6	15
4510083		1	2.4 - 2.8	100	-	9.6	15
4510093		1	2.4 - 2.8	100	-	9.6	15
4510043		1	2.4 - 2.8	100	-	9.6	15
4510053		1	2.4 - 2.8	100	-	9.6	15
4510063		1	2.4 - 2.8	100	-	9.6	15
4510163		1	2.4 - 2.8	100	-	9.6	15
4510923	/	1	2.4 - 2.8	100	-	9.6	15
4510001S	/	0.5	2.1 - 2.5	-	250	4.8	9
4510011S		0.5	2.1 - 2.5	-	250	4.8	9
4510021S		0.5	2.1 - 2.5	-	250	4.8	9
4510141S		0.5	2.1 - 2.5	-	250	4.8	9
4510031S		0.5	2.1 - 2.5	-	250	4.8	9
4510111S		0.5	2.1 - 2.5	-	250	4.8	9
4510121S		0.5	2.1 - 2.5	-	250	4.8	9
4510071S		0.5	2.1 - 2.5	-	250	4.8	9
4510081S		0.5	2.1 - 2.5	-	250	4.8	9
4510091S		0.5	2.1 - 2.5	-	250	4.8	9
4510101S		0.5	2.1 - 2.5	-	250	4.8	9
4510041S		0.5	2.1 - 2.5	-	250	4.8	9
4510051S		0.5	2.1 - 2.5	-	250	4.8	9
4510061S		0.5	2.1 - 2.5	-	250	4.8	9
4510002S	/	0.75	2.2 - 2.7	-	250	7.2	12
4510012S		0.75	2.2 - 2.7	-	250	7.2	12
4510022S		0.75	2.2 - 2.7	-	250	7.2	12
4510142S		0.75	2.2 - 2.7	-	250	7.2	12
4510032S		0.75	2.2 - 2.7	-	250	7.2	12
4510112S		0.75	2.2 - 2.7	-	250	7.2	12
4510122S		0.75	2.2 - 2.7	-	250	7.2	12
4510072S		0.75	2.2 - 2.7	-	250	7.2	12
4510082S		0.75	2.2 - 2.7	-	250	7.2	12

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

		(mm <sup>2</sup> )	(mm)	m/	m/	(kg/km)	(kg/km)
4510092S		0.75	2.2 - 2.7	-	250	7.2	12
4510102S		0.75	2.2 - 2.7	-	250	7.2	12
4510042S		0.75	2.2 - 2.7	-	250	7.2	12
4510052S		0.75	2.2 - 2.7	-	250	7.2	12
4510062S		0.75	2.2 - 2.7	-	250	7.2	12
4510162S		0.75	2.2 - 2.7	-	250	7.2	12
4510003S	/	1	2.4 - 2.8	-	250	9.6	15
4510013S		1	2.4 - 2.8	-	250	9.6	15
4510023S		1	2.4 - 2.8	-	250	9.6	15
4510143S		1	2.4 - 2.8	-	250	9.6	15
4510033S		1	2.4 - 2.8	-	250	9.6	15
4510113S		1	2.4 - 2.8	-	250	9.6	15
4510123S		1	2.4 - 2.8	-	250	9.6	15
4510073S		1	2.4 - 2.8	-	250	9.6	15
4510083S		1	2.4 - 2.8	-	250	9.6	15
4510093S		1	2.4 - 2.8	-	250	9.6	15
4510103S		1	2.4 - 2.8	-	250	9.6	15
4510043S		1	2.4 - 2.8	-	250	9.6	15
4510053S		1	2.4 - 2.8	-	250	9.6	15
4510063S		1	2.4 - 2.8	-	250	9.6	15
4510163S		1	2.4 - 2.8	-	250	9.6	15
Maxi							
4510011X		0.5	2.1 - 2.5	600	-	4.8	9
4510021X		0.5	2.1 - 2.5	600	-	4.8	9
4510141X		0.5	2.1 - 2.5	600	-	4.8	9
4510061X		0.5	2.1 - 2.5	600	-	4.8	9
4510041X		0.5	2.1 - 2.5	600	-	4.8	9
4510051X		0.5	2.1 - 2.5	600	-	4.8	9
4510012X		0.75	2.2 - 2.7	500	-	9.6	13
4510022X		0.75	2.2 - 2.7	500	-	7.2	13
4510142X		0.75	2.2 - 2.7	500	-	7.2	13
4510002X	/	0.75	2.2 - 2.7	500	-	7.2	13
4510062X		0.75	2.2 - 2.7	500	-	7.2	13
4510092X		0.75	2.2 - 2.7	500	-	7.2	13

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# H05V-K <HAR>

		(mm <sup>2</sup> )	(mm)	m/	m/	(kg/km)	(kg/km)
4510042X		0.75	2.2 - 2.7	500	-	7.2	13
4510072X		0.75	2.2 - 2.7	500	-	7.2	13
4510052X		0.75	2.2 - 2.7	500	-	7.2	13
4510013X		1.0	2.4 - 2.8	400	-	9.6	15
4510033X		1.0	2.4 - 2.8	400	-	9.6	15
4510023X		1.0	2.4 - 2.8	400	-	9.6	15
4510143X		1.0	2.4 - 2.8	400	-	9.6	15
4510003X	/	1.0	2.4 - 2.8	400	-	9.6	15
4510063X		1.0	2.4 - 2.8	400	-	9.6	15
4510093X		1.0	2.4 - 2.8	400	-	9.6	15
4510043X		1.0	2.4 - 2.8	400	-	9.6	15
4510053X		1.0	2.4 - 2.8	400	-	9.6	15

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# H05V-K <HAR>



(24.04.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>  
data sheet

PN 0456 / 02\_03.16