

N2XSY

PVC ()

VDE 0276-620 N2XSY, VDE, PVC (), ,

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV



EVU
HD 620/VDE 0276-620 10-C (4)
0.6m, 0.8m 가 :

: IEC 60332-1-2
HD 620/VDE 0276-620, 10-C, 7 , (HD 620/VDE 0276-620, Part 10-C, 5
+20 °C)
가 +30 °C): VDE 0298-4, VDE 0298-4 ,
. (T12) /

HD 620/ VDE 0276-620

"rm": r = , m =
: 가 (XLPE)

: PVC,

(24.04.2024)

N2XSY

ETIM 5:

ETIM 5.0 Class-ID: EC001140

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001140

ETIM 6.0 Class :

:

:

: 15 x

:

U₀/U: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV

:

6/10 kV: 15 kV, 12/20 kV: 30 kV, 18/30

:

kV: 45 kV

: -5°C ~ +90°C

: -40°C ~ +90°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths

가 VAT

가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
6/10 (12) kV				
3037523	1X35 RM/16	24	518	867
3022192	1X50 RM/16	25	662	1001
38007455	1X70 RM/16	26	854	1232
3037524	1X95 RM/16	28	1094	1500
38101056	1X120 RM/16	30	1334	1746
1550537	1X150 RM/25	31	1723	2095
38007456	1X185 RM/25	33	2059	2472
1550538	1X240 RM/25	35	2587	3032
38100269	1X300 RM/25	37	3163	3637
38101815	1X400 RM/35	40	4234	4535
38101814	1X500 RM/35	43	5194	5566
38107775	1x630 RM/35	47	6442	6935
12/20 (24) kV				
1552067	1X35 RM/16	28	518	1030
1552040	1X50 RM/16	29	662	1169
38300006	1X70 RM/16	31	854	1410
3801425	1X95 RM/16	32	1094	1689
38100617	1X120 RM/16	34	1334	1944
1550554	1X150 RM/25	35	1723	2301
38107776	1x185 RM/25	37	2059	2689
38300015	1X240 RM/25	39	2587	3262
38300017	1X300 RM/25	42	3163	3882
38101817	1X400 RM/35	44	4234	4797
38101816	1X500 RM/35	47	5194	5850
38107777	1x630 RM/35	51	6442	7237
38107778	1x800 RM/35	56	8074	9058
18/30 (36) kV				
38107779	1x35 RM/16	24	518	770
38300014	1X50 RM/16	34	662	1403
38107780	1x70 RM/16	36	854	1656
38801995	1X95 RM/16	37	1094	1947
38300009	1X120 RM/16	39	1334	2213
38107781	1x150 RM/25	40	1723	2580



N2XSY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
38107782	1x185 RM/25	42	2059	2980
38106711	1X240 RM/25	44	2587	3570
38107783	1x300 RM/25	47	3163	4208
38107784	1x400 RM/35	50	4234	5147
38107785	1x500 RM/35	53	5194	6244

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16