

# H07V2-K

Ideally suited to meet the stricter thermal requirements of the new IEC-EN-(NBN NEN) 61439 standard

90°C



<HAR> 가 ( : <VDE><HAR> )  
<HAR> 가

Ideally suited to meet the stricter thermal requirements of the new IEC-EN-(NBN NEN) 61439 standard

: IEC 60332-1-2

EN 50525-2-31

5(IEC 60228 ) 가 가  
: PVC, 90°C, TI3

ETIM 5:

ETIM 5.0 Class-ID: EC000993  
ETIM 5.0 Class :

(24.04.2024)



# H07V2-K

:	VDE 0295	5/ IEC 60228	5
:	가	가	
:	4x Außendurchmesser		
:	U0/U: 450/750 V		
:	2500 V		
:	-10°C ~ +90°C		
:	: 5°C		

가 VAT 가 가 . 가 가 ( . ) 가 .

		(mm <sup>2</sup> )	(mm)	m/	(kg/km)	(kg/km)
4519001	/	1.5	3.4	100	14.4	22
4519002	/	2.5	4.1	100	24	31
4519003	/	4	4.8	100	38.4	45
4519004	/	6	5.3	100	57.6	65
4519005	/	10	6.8	100	96	109
4519006	/	16	8.1	100	153.6	163
4519007	/	25	10.2	100	240	251
4519008	/	35	11.7	50	336	350
4519011		1.5	3.4	100	14.4	22
4519012		2.5	4.1	100	24	31
4519013		4	4.8	100	38.4	45
4519014		6	5.3	100	57.6	65
4519015		10	6.8	100	96	109
4519016		16	8.1	100	153.6	163
4519017		25	10.2	100	240	251
4519018		35	11.7	50	336	350
4519021		1.5	3.4	100	14.4	22
4519022		2.5	4.1	100	24	31
4519023		4	4.8	100	38.4	45
4519024		6	5.3	100	57.6	65
4519025		10	6.8	100	96	109
4519026		16	8.1	100	153.6	163
4519027		25	10.2	100	240	251
4519028		35	11.7	50	336	350
4519141		1.5	3.4	100	14.4	22
4519142		2.5	4.1	100	24	31
4519143		4	4.8	100	38.4	45
4519144		6	5.3	100	57.6	65
4519145		10	6.8	100	96	109
4519146		16	8.1	100	153.6	163
4519031		1.5	3.4	100	14.4	22
4519032		2.5	4.1	100	24	31
4519033		4	4.8	100	38.4	45
4519034		6	5.3	100	57.6	65

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16

		(mm <sup>2</sup> )	(mm)	m/	(kg/km)	(kg/km)
4519035		10	6.8	100	96	109
4519036		16	8.1	100	153.6	163
4519071		1.5	3.4	100	14.4	22
4519072		2.5	4.1	100	24	31
4519091		1.5	3.4	100	14.4	22
4519092		2.5	4.1	100	24	31
4519093		4	4.8	100	38.4	45
4519094		6	5.3	100	57.6	65
4519095		10	6.8	100	96	109
4519096		16	8.1	100	153.6	163
4519041		1.5	3.4	100	14.4	22
4519042		2.5	4.1	100	24	31
4519043		4	4.8	100	38.4	45
4519044		6	5.3	100	57.6	65
4519045		10	6.8	100	96	109
4519046		16	8.1	100	153.6	163
4519047		25	10.2	100	240	251
4519048		35	11.7	50	336	350
4519051		1.5	3.4	100	14.4	22
4519052		2.5	4.1	100	24	31
4519053		4	4.8	100	38.4	45
4519054		6	5.3	100	57.6	65
4519061		1.5	3.4	100	14.4	22
4519062		2.5	4.1	100	24	31
4519063		4	4.8	100	38.4	45
4519064		6	5.3	100	57.6	65
4519065		10	6.8	100	96	109
4519066		16	8.1	100	153.6	163
4519081		1.5	3.4	100	14.4	22
4519009	/	50	13.9	-	480	559

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16