

## X07V-K with twin colour helix insulation

X07V-K, , PVC, 450/750 V, class 5, , ,

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)  
PVC



가 , (trough),

: IEC 60332-1-2  
: d1 = 18 mm; d2 = 200 mm; b = 85 mm

EN 50525-2-31

5(IEC 60228 )  
: PVC

가 가

ETIM 5:

ETIM 5.0 Class-ID: EC000993  
ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993  
ETIM 6.0 Class :

:

VDE 0295 5/ IEC 60228 5  
가 가

:

4 x (OD) H07V-K

(24.04.2024)



# X07V-K with twin colour helix insulation

:	2 x OD
:	U0/U: 450/750 V
:	2500 V
:	VDE 0298 4
:	EN 50565-1/ VDE 0298-565-1
:	: -40°C +70°C

가 가 ( . ) 가 .  
 ,  
 가 VAT 가 가 .

## X07V-K with twin colour helix insulation

		(mm <sup>2</sup> )	(mm)	m/	(kg/km)	(kg/km)
4522261S	/	1.5	2.8 - 3.4	150	14.4	22
4522921S	/	1.5	2.8 - 3.4	150	14.4	22
4522201S	/	1.5	2.8 - 3.4	150	14.4	22
4522211S	/	1.5	2.8 - 3.4	150	14.4	22
4522231S	/	1.5	2.8 - 3.4	150	14.4	22
4522241S	/	1.5	2.8 - 3.4	150	14.4	22
4522251S	/	1.5	2.8 - 3.4	150	14.4	22
4522291S	/	1.5	2.8 - 3.4	150	14.4	22
4522311S	-	1.5	2.8 - 3.4	150	14.4	22
4522331S	-	1.5	2.8 - 3.4	150	14.4	22
4522371S	-	1.5	2.8 - 3.4	150	14.4	22
4522381S	-	1.5	2.8 - 3.4	150	14.4	22
4522391S	-	1.5	2.8 - 3.4	150	14.4	22
4522401S	-	1.5	2.8 - 3.4	150	14.4	22
4522411S	-	1.5	2.8 - 3.4	150	14.4	22
4522421S	-	1.5	2.8 - 3.4	150	14.4	22
4522441S	-	1.5	2.8 - 3.4	150	14.4	22
4522461S	-	1.5	2.8 - 3.4	150	14.4	22
4522341S	-	1.5	2.8 - 3.4	150	14.4	22
4522221S	/	1.5	2.8 - 3.4	150	14.4	22
4522301S	-	1.5	2.8 - 3.4	150	14.4	22
4522321S	-	1.5	2.8 - 3.4	150	14.4	22
4522431S	=	1.5	2.8 - 3.4	150	14.4	22
4522471S	-	1.5	2.8 - 3.4	150	14.4	22
4522262S	/	2.5	3.4 - 4.1	100	24	37
4522922S	/	2.5	3.4 - 4.1	100	24	37
4522252S	/	2.5	3.4 - 4.1	100	24	37
4522292S	/	2.5	3.4 - 4.1	100	24	37
4522372S	-	2.5	3.4 - 4.1	100	24	37
4522392S	-	2.5	3.4 - 4.1	100	24	37
4522402S	-	2.5	3.4 - 4.1	100	24	37
4522422S	-	2.5	3.4 - 4.1	100	24	37
4522442S	-	2.5	3.4 - 4.1	100	24	37
4522462S	-	2.5	3.4 - 4.1	100	24	37

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## X07V-K with twin colour helix insulation

		(mm <sup>2</sup> )	(mm)	m/	(kg/km)	(kg/km)
4522222S	/	2.5	3.4 - 4.1	100	24	37
4522472S	-	2.5	3.4 - 4.1	100	24	37

(24.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

X07V-K with twin colour helix insulation



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16