



H07Z-K 90°C

Harmonised,

H07Z-K 90°C, HAR,

450 / 750V

CPR: www.lappkabel.com/cpr

(HAR)

ÖLFLEX® HEAT 125 SC



가 가 가

ÖLFLEX® HEAT 125 SC

가

IEC 61034
: IEC 60332-1-2

(25.04.2024)

H07Z-K 90°C

<HAR>EN 50525-3-41
EN 50525-1/ VDE 0285-525-1
(- , -)

: , (), (),

가

:

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

VDE 0295 5/ IEC 60228 5

가 가

:

EN 50565-1

OD 8 mm: 4 x OD*/2 x OD**;

8 < OD 12 mm: 5 x OD*/3 x OD**;

OD > 12 mm: 6 x OD*/4 x OD**

:

U0/U: 450/ 750 V

:

2500 V

:

VDE 0298-4

EN 50565-1/ VDE 0298-565-1

:

: -5°C ~ +90°C

: -40°C ~ +90°C

: 30 kg,

가

가

(.)

가

가

VAT

가

가

*

,**

; "OD" =

	(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4726001S	1.5	2.8 - 3.5	/	-	-	150	14.4	20
4726121S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726031S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726011S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726061S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726021S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726141S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726091S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726071S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726111S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726051S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726041S	1.5	2.8 - 3.5		-	-	150	14.4	20
4726002S	2.5	3.4 - 4.3	/	-	-	100	24	32
4726122S	2.5	3.4 - 4.3		-	-	100	24	32
4726032S	2.5	3.4 - 4.3		-	-	100	24	32
4726012S	2.5	3.4 - 4.3		-	-	100	24	32
4726062S	2.5	3.4 - 4.3		-	-	100	24	32
4726022S	2.5	3.4 - 4.3		-	-	100	24	32
4726142S	2.5	3.4 - 4.3		-	-	100	24	32
4726092S	2.5	3.4 - 4.3		-	-	100	24	32
4726072S	2.5	3.4 - 4.3		-	-	100	24	32
4726112S	2.5	3.4 - 4.3		-	-	100	24	32
4726052S	2.5	3.4 - 4.3		-	-	100	24	32
4726042S	2.5	3.4 - 4.3		-	-	100	24	32
4726001	1.5	2.8 - 3.5	/	100	-	-	14.4	20
4726001K	1.5	2.8 - 3.5	/	-	1500	-	14.4	20
4726121	1.5	2.8 - 3.5		100	-	-	14.4	20
4726121K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726031	1.5	2.8 - 3.5		100	-	-	14.4	20
4726031K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726011	1.5	2.8 - 3.5		100	-	-	14.4	20
4726011K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726061	1.5	2.8 - 3.5		100	-	-	14.4	20
4726061K	1.5	2.8 - 3.5		-	1500	-	14.4	20

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

	(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4726021	1.5	2.8 - 3.5		100	-	-	14.4	20
4726021K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726141	1.5	2.8 - 3.5		100	-	-	14.4	20
4726141K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726091	1.5	2.8 - 3.5		100	-	-	14.4	20
4726091K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726071	1.5	2.8 - 3.5		100	-	-	14.4	20
4726071K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726111	1.5	2.8 - 3.5		100	-	-	14.4	20
4726111K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726051	1.5	2.8 - 3.5		100	-	-	14.4	20
4726051K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726041	1.5	2.8 - 3.5		100	-	-	14.4	20
4726041K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726081	1.5	2.8 - 3.5		100	-	-	14.4	20
4726081K	1.5	2.8 - 3.5		-	1500	-	14.4	20
4726261K	1.5	2.8 - 3.5	/	-	1500	-	14.4	20
4726002	2.5	3.4 - 4.3	/	100	-	-	24	32
4726002K	2.5	3.4 - 4.3	/	-	900	-	24	32
4726122	2.5	3.4 - 4.3		100	-	-	24	32
4726122K	2.5	3.4 - 4.3		-	900	-	24	32
4726032	2.5	3.4 - 4.3		100	-	-	24	32
4726032K	2.5	3.4 - 4.3		-	900	-	24	32
4726012	2.5	3.4 - 4.3		100	-	-	24	32
4726012K	2.5	3.4 - 4.3		-	900	-	24	32
4726062	2.5	3.4 - 4.3		100	-	-	24	32
4726062K	2.5	3.4 - 4.3		-	900	-	24	32
4726022	2.5	3.4 - 4.3		100	-	-	24	32
4726022K	2.5	3.4 - 4.3		-	900	-	24	32
4726142	2.5	3.4 - 4.3		100	-	-	24	32
4726142K	2.5	3.4 - 4.3		-	900	-	24	32
4726092	2.5	3.4 - 4.3		100	-	-	24	32
4726092K	2.5	3.4 - 4.3		-	900	-	24	32
4726072	2.5	3.4 - 4.3		100	-	-	24	32

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

	(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4726072K	2.5	3.4 - 4.3		-	900	-	24	32
4726112	2.5	3.4 - 4.3		100	-	-	24	32
4726112K	2.5	3.4 - 4.3		-	900	-	24	32
4726052	2.5	3.4 - 4.3		100	-	-	24	32
4726052K	2.5	3.4 - 4.3		-	900	-	24	32
4726042	2.5	3.4 - 4.3		100	-	-	24	32
4726042K	2.5	3.4 - 4.3		-	900	-	24	32
4726082	2.5	3.4 - 4.3		100	-	-	24	32
4726082K	2.5	3.4 - 4.3		-	900	-	24	32
4726262K	2.5	3.4 - 4.3	/	-	900	-	24	32
4726003	4	3.9 - 4.9	/	100	-	-	38.4	45
4726003K	4	3.9 - 4.9	/	-	600	-	38.4	45
4726123	4	3.9 - 4.9		100	-	-	38.4	45
4726123K	4	3.9 - 4.9		-	600	-	38.4	45
4726033	4	3.9 - 4.9		100	-	-	38.4	45
4726033K	4	3.9 - 4.9		-	600	-	38.4	45
4726013	4	3.9 - 4.9		100	-	-	38.4	45
4726013K	4	3.9 - 4.9		-	600	-	38.4	45
4726063	4	3.9 - 4.9		100	-	-	38.4	45
4726063K	4	3.9 - 4.9		-	600	-	38.4	45
4726023	4	3.9 - 4.9		100	-	-	38.4	45
4726023K	4	3.9 - 4.9		-	600	-	38.4	45
4726143	4	3.9 - 4.9		100	-	-	38.4	45
4726143K	4	3.9 - 4.9		-	600	-	38.4	45
4726093	4	3.9 - 4.9		100	-	-	38.4	45
4726093K	4	3.9 - 4.9		-	600	-	38.4	45
4726073	4	3.9 - 4.9		100	-	-	38.4	45
4726073K	4	3.9 - 4.9		-	600	-	38.4	45
4726113	4	3.9 - 4.9		100	-	-	38.4	45
4726113K	4	3.9 - 4.9		-	600	-	38.4	45
4726053	4	3.9 - 4.9		100	-	-	38.4	45
4726053K	4	3.9 - 4.9		-	600	-	38.4	45
4726043	4	3.9 - 4.9		100	-	-	38.4	45
4726043K	4	3.9 - 4.9		-	600	-	38.4	45

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

		(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4726083	4		3.9 - 4.9		100	-	-	38.4	45
4726083K	4		3.9 - 4.9		-	600	-	38.4	45
4726004	6		4.4 - 5.5	/	100	-	-	57.6	65
4726004K	6		4.4 - 5.5	/	-	400	-	57.6	65
4726124	6		4.4 - 5.5		100	-	-	57.6	65
4726124K	6		4.4 - 5.5		-	400	-	57.6	65
4726034	6		4.4 - 5.5		100	-	-	57.6	65
4726034K	6		4.4 - 5.5		-	400	-	57.6	65
4726014	6		4.4 - 5.5		100	-	-	57.6	65
4726014K	6		4.4 - 5.5		-	400	-	57.6	65
4726064	6		4.4 - 5.5		100	-	-	57.6	65
4726064K	6		4.4 - 5.5		-	400	-	57.6	65
4726024	6		4.4 - 5.5		100	-	-	57.6	65
4726024K	6		4.4 - 5.5		-	400	-	57.6	65
4726144	6		4.4 - 5.5		100	-	-	57.6	65
4726144K	6		4.4 - 5.5		-	400	-	57.6	65
4726094	6		4.4 - 5.5		100	-	-	57.6	65
4726094K	6		4.4 - 5.5		-	400	-	57.6	65
4726074	6		4.4 - 5.5		100	-	-	57.6	65
4726074K	6		4.4 - 5.5		-	400	-	57.6	65
4726114	6		4.4 - 5.5		100	-	-	57.6	65
4726114K	6		4.4 - 5.5		-	400	-	57.6	65
4726054	6		4.4 - 5.5		100	-	-	57.6	65
4726054K	6		4.4 - 5.5		-	400	-	57.6	71
4726044	6		4.4 - 5.5		100	-	-	57.6	65
4726044K	6		4.4 - 5.5		-	400	-	57.6	65
4726084	6		4.4 - 5.5		100	-	-	57.6	65
4726084K	6		4.4 - 5.5		-	400	-	57.6	65
4726005	10		5.7 - 7.1	/	100	-	-	96	110
4726125	10		5.7 - 7.1		100	-	-	96	110
4726035	10		5.7 - 7.1		100	-	-	96	110
4726015	10		5.7 - 7.1		100	-	-	96	110
4726065	10		5.7 - 7.1		100	-	-	96	110
4726025	10		5.7 - 7.1		100	-	-	96	110

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

	(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4726145	10	5.7 - 7.1		100	-	-	96	110
4726095	10	5.7 - 7.1		100	-	-	96	110
4726075	10	5.7 - 7.1		100	-	-	96	110
4726115	10	5.7 - 7.1		100	-	-	96	110
4726055	10	5.7 - 7.1		100	-	-	96	110
4726045	10	5.7 - 7.1		100	-	-	96	110
4726085	10	5.7 - 7.1		100	-	-	96	110
4726006	16	6.7 - 8.4	/	100	-	-	153.6	170
4726126	16	6.7 - 8.4		100	-	-	153.6	170
4726036	16	6.7 - 8.4		100	-	-	153.6	170
4726016	16	6.7 - 8.4		100	-	-	153.6	170
4726066	16	6.7 - 8.4		100	-	-	153.6	170
4726026	16	6.7 - 8.4		100	-	-	153.6	170
4726146	16	6.7 - 8.4		100	-	-	153.6	170
4726096	16	6.7 - 8.4		100	-	-	153.6	170
4726076	16	6.7 - 8.4		100	-	-	153.6	170
4726116	16	6.7 - 8.4		100	-	-	153.6	170
4726056	16	6.7 - 8.4		100	-	-	153.6	170
4726046	16	6.7 - 8.4		100	-	-	153.6	170
4726086	16	6.7 - 8.4		100	-	-	153.6	170
4726007	25	8.4 - 10.6	/	100	-	-	240	290
4726127	25	8.4 - 10.6		100	-	-	240	290
4726037	25	8.4 - 10.6		100	-	-	240	290
4726017	25	8.4 - 10.6		100	-	-	240	290
4726067	25	8.4 - 10.6		100	-	-	240	290
4726027	25	8.4 - 10.6		100	-	-	240	290
4726147	25	8.4 - 10.6		100	-	-	240	290
4726097	25	8.4 - 10.6		100	-	-	240	290
4726077	25	8.4 - 10.6		100	-	-	240	290
4726117	25	8.4 - 10.6		100	-	-	240	290
4726057	25	8.4 - 10.6		100	-	-	240	290
4726047	25	8.4 - 10.6		100	-	-	240	290
4726087	25	8.4 - 10.6		100	-	-	240	290
4726008	35	9.7 - 12.1	/	-	-	-	336	380

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

		(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4726128	35		9.7 - 12.1		-	-	-	336	380
4726038	35		9.7 - 12.1		-	-	-	336	380
4726018	35		9.7 - 12.1		-	-	-	336	380
4726068	35		9.7 - 12.1		-	-	-	336	380
4726028	35		9.7 - 12.1		-	-	-	336	380
4726148	35		9.7 - 12.1		-	-	-	336	380
4726098	35		9.7 - 12.1		-	-	-	336	380
4726078	35		9.7 - 12.1		-	-	-	336	380
4726118	35		9.7 - 12.1		-	-	-	336	380
4726058	35		9.7 - 12.1		-	-	-	336	380
4726048	35		9.7 - 12.1		-	-	-	336	380
4726088	35		9.7 - 12.1		-	-	-	336	380
4726009	50		11.5 - 14.4	/	-	-	-	480	530
4726129	50		11.5 - 14.4		-	-	-	480	530
4726039	50		11.5 - 14.4		-	-	-	480	530
4726019	50		11.5 - 14.4		-	-	-	480	530
4726069	50		11.5 - 14.4		-	-	-	480	530
4726029	50		11.5 - 14.4		-	-	-	480	530
4726149	50		11.5 - 14.4		-	-	-	480	530
4726099	50		11.5 - 14.4		-	-	-	480	530
4726079	50		11.5 - 14.4		-	-	-	480	530
4726119	50		11.5 - 14.4		-	-	-	480	530
4726059	50		11.5 - 14.4		-	-	-	480	530
4726049	50		11.5 - 14.4		-	-	-	480	530
4726089	50		11.5 - 14.4		-	-	-	480	530
4727001	70		13.2 - 16.6	/	-	-	-	672	750
4727121	70		13.2 - 16.6		-	-	-	672	750
4727031	70		13.2 - 16.6		-	-	-	672	750
4727011	70		13.2 - 16.6		-	-	-	672	750
4727061	70		13.2 - 16.6		-	-	-	672	750
4727021	70		13.2 - 16.6		-	-	-	672	750
4727141	70		13.2 - 16.6		-	-	-	672	750
4727091	70		13.2 - 16.6		-	-	-	672	750
4727071	70		13.2 - 16.6		-	-	-	672	750

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



H07Z-K 90°C

	(mm ²)	(mm)		m/	m/box	m/	(kg/km)	(kg/km)
4727111	70	13.2 - 16.6		-	-	-	672	750
4727051	70	13.2 - 16.6		-	-	-	672	750
4727041	70	13.2 - 16.6		-	-	-	672	750
4727081	70	13.2 - 16.6		-	-	-	672	750
4727002	95	15.1 - 18.8	/	-	-	-	912	1000
4727122	95	15.1 - 18.8		-	-	-	912	1000
4727032	95	15.1 - 18.8		-	-	-	912	1000
4727012	95	15.1 - 18.8		-	-	-	912	1000
4727062	95	15.1 - 18.8		-	-	-	912	1000
4727022	95	15.1 - 18.8		-	-	-	912	1000
4727142	95	15.1 - 18.8		-	-	-	912	1000
4727092	95	15.1 - 18.8		-	-	-	912	1000
4727072	95	15.1 - 18.8		-	-	-	912	1000
4727112	95	15.1 - 18.8		-	-	-	912	1000
4727052	95	15.1 - 18.8		-	-	-	912	1000
4727042	95	15.1 - 18.8		-	-	-	912	1000
4727082	95	15.1 - 18.8		-	-	-	912	1000

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



H07Z-K 90°C



(25.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16