


# ÖLFLEX® CRANE F

ÖLFLEX® CRANE F -  
ø/U: 300/500V

/

.

, U



가

50m

가

ÖLFLEX® CRANE

ÖLFLEX(R) LIFT

A3

(24.04.2024)

# ÖLFLEX® CRANE F

: IEC 60332-1-2

VDE 0250(NGFLGÖU)

:  
:  
:

ETIM 5:

ETIM 5.0 Class-ID: EC000825  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000825  
ETIM 6.0 Class :

:

5 : VDE 0293-308 . T9  
6 :

:

VDE 0295/IEC 60228  
25 mm<sup>2</sup> : , class 6

35 mm<sup>2</sup> : , class 5

:

: 10 x  
: 4 x

:

U0/U: 300/500 V

:

3000 V

:

G = GN/YE

X = GN/YE

:

: -25°C ~ +90°C  
: -40°C ~ +90°C

:

가 가 ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)



# ÖLFLEX® CRANE F

	(CORE) / (mm <sup>2</sup> )	, x (mm)	(kg/km)	(kg/km)
ÖLFLEX® CRANE F				
0041041	4.0 G 1.5	17.5 x 6.2	57.6	200
0041042	5.0 G 1.5	21.5 x 6.2	72	240
0041043	7.0 G 1.5	29 x 6.2	100.8	360
0041044	8.0 G 1.5	31.5 x 6.2	115	370
0041045	10.0 G 1.5	40 x 6.5	144	520
0041046	12.0 G 1.5	47 x 6.5	172.8	620
0041047	4.0 G 2.5	21 x 7.5	96	280
0041048	5.0 G 2.5	27 x 7.5	120	400
0041049	7.0 G 2.5	35 x 7.5	168	520
0041050	8.0 G 2.5	39 x 7.5	192	550
0041051	12.0 G 2.5	56 x 8	288	800
0041052	4.0 G 4.0	26 x 9	153.6	410
0041053	7.0 G 4.0	42 x 9	268.8	700
0041054	4.0 G 6.0	29 x 9.5	230	600
0041056	7.0 G 6.0	42 x 9.5	403	850
0041057	4.0 G 10.0	33 x 11	384	800
0041059	4.0 G 16.0	38 x 13	614	1150
0041060	4.0 G 25.0	49.5 x 15	960	1700
0041061	4.0 G 35.0	55 x 17	1344	2360

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16