

# ÖLFLEX® CRANE 2ST

, 가 PVC

ÖLFLEX® CRANE 2ST PVC , , U  
0/U: 300/500 V

, ÖLFLEX® CRANE 2S



2100 N

;

ÖLFLEX® CRANE

ÖLFLEX(R) LIFT

A3

(26.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® CRANE 2ST

: IEC 60332-1-2

VDE 0250

PVC-

PVC-

,

ETIM 5:

ETIM 5.0 Class-ID: EC000104

ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104

ETIM 6.0 Class :

:

Black with white numbers acc. to VDE 0293-334

:

VDE 0295 class 6, IEC 60228 class 6

가

:

: 20 x

:

U0/U: 300/500 V

:

4000 V

:

G = GN/YE

X = GN/YE

:

: -15°C +70°C

, 가 가 ( . ) 가 .

[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

: 30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(26.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® CRANE 2ST

	(CORE) / (mm <sup>2</sup> )	Cable Ø (mm)	strain wire (mm)	(kg/km)	(kg/km)
2027503	8.0 G 1.5	13.6	19	115	430
2027504	12.0 G 1.5	15.5	21	172.8	510
2027505	20.0 G 1.5	20	25	288	720

(26.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16