


H05V2-K

Ideally suited to meet the stricter thermal requirements of the new IEC-EN-(NBN NEN) 61439 standard

90°C



<HAR> 가 (: <VDE><HAR>)
<HAR> 가

Ideally suited to meet the stricter thermal requirements of the new IEC-EN-(NBN NEN) 61439 standard

: IEC 60332-1-2

EN 50525-2-31

5(IEC 60228) 가 가
: PVC, 90°C, T13

ETIM 5:

ETIM 5.0 Class-ID: EC000993
ETIM 5.0 Class :

(24.04.2024)



H05V2-K

:	VDE 0295	5/ IEC 60228	5
:	가	가	
:	4x Außendurchmesser		
:	U0/U: 300/500 V		
:	2000 V		
:	-10°C ~ +90°C		
:	: 5°C		

www.lappkabel.de/en/cable-standradlengths (.) 가 .

가 VAT 가 가 .

(24.04.2024)

		(mm ²)	(mm)	m/	(kg/km)	(kg/km)
4515001	/	0.5	2.5	100	4.8	9
4515002	/	0.75	2.7	100	7.2	11
4515003	/	1	2.8	100	9.6	14
4515011		0.5	2.5	100	4.8	9
4515012		0.75	2.7	100	7.2	11
4515013		1	2.8	100	9.6	14
4515021		0.5	2.5	100	4.8	9
4515022		0.75	2.7	100	7.2	11
4515023		1	2.8	100	9.6	14
4515141		0.5	2.5	100	4.8	9
4515142		0.75	2.7	100	7.2	11
4515143		1	2.8	100	9.6	14
4515031		0.5	2.5	100	4.8	9
4515032		0.75	2.7	100	7.2	11
4515033		1	2.8	100	9.6	14
4515111		0.5	2.5	100	4.8	9
4515112		0.75	2.7	100	7.2	11
4515113		1	2.8	100	9.6	14
4515121		0.5	2.5	100	4.8	9
4515122		0.75	2.7	100	7.2	11
4515123		1	2.8	100	9.6	14
4515071		0.5	2.5	100	4.8	9
4515072		0.75	2.7	100	7.2	11
4515073		1	2.8	100	9.6	14
4515081		0.5	2.5	100	4.8	9
4515082		0.75	2.7	100	7.2	11
4515083		1	2.8	100	9.6	14
4515091		0.5	2.5	100	4.8	9
4515092		0.75	2.7	100	7.2	11
4515093		1	2.8	100	9.6	14
4515041		0.5	2.5	100	4.8	9
4515042		0.75	2.7	100	7.2	11
4515043		1	2.8	100	9.6	14
4515051		0.5	2.5	100	4.8	9

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



H05V2-K

		(mm ²)	(mm)	m/	(kg/km)	(kg/km)
4515052		0.75	2.7	100	7.2	11
4515053		1	2.8	100	9.6	14
4515061		0.5	2.5	100	4.8	9
4515062		0.75	2.7	100	7.2	11
4515063		1	2.8	100	9.6	14
4515923	/	1	2.8	100	9.6	14

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16