

LiY

LIY, , PVC, , , . + 70 ° C

PVC



: IEC 60332-1-2
: d1 = 18 mm; d2 = 150 mm; b = 85 mm

VDE 0812

: VDE 0207-4 PVC , type YI 2/ I 2

ETIM 5:

ETIM 5.0 Class-ID: EC000993
ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993
ETIM 6.0 Class :

:

500 V (0.14 mm²)

900 V (0.25 sq.mm)

(23.04.2024)

LiY

：	0.14 mm ² : ≥ 18 (0.10 mm Ø)
	0.25 mm ² : ≥ 14 가 (0.15 mm Ø)
：	< 50 VAC
	UPP - - - : ≤ 250 V
：	1200 V (0.14 mm ²)
	2500 V (0.25 mm ²)
：	: -30°C +70°C

가 가 (.) 가 .
 ,
 가 VAT 가 가 .

		(mm ²)	(mm)	m/	(kg/km)
4125000S	/	0.14	1.1	500	1.35
4125001S		0.14	1.1	500	1.35
4125002S		0.14	1.1	500	1.35
4125014S		0.14	1.1	500	1.35
4125003S		0.14	1.1	500	1.35
4125005S		0.14	1.1	500	1.35
4125006S		0.14	1.1	500	1.35
4125007S		0.14	1.1	500	1.35
4125008S		0.14	1.1	500	1.35
4125009S		0.14	1.1	500	1.35
4125104S		0.14	1.1	500	1.35
4125105S		0.14	1.1	500	1.35
4125106S		0.14	1.1	500	1.35
4126000S	/	0.25	1.3	250	2.4
4126001S		0.25	1.3	250	2.4
4126002S		0.25	1.3	250	2.4
4126014S		0.25	1.3	250	2.4
4126003S		0.25	1.3	250	2.4
4126004S		0.25	1.3	250	2.4
4126005S		0.25	1.3	250	2.4
4126006S		0.25	1.3	250	2.4
4126007S		0.25	1.3	250	2.4
4126008S		0.25	1.3	250	2.4
4126009S		0.25	1.3	250	2.4
4126010S		0.25	1.3	250	2.4
4126104S		0.25	1.3	250	2.4
4126105S		0.25	1.3	250	2.4
4126106S		0.25	1.3	250	2.4

(23.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

LiY



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16