

ÖLFLEX® HEAT 125 MC 450/750 V


가

가

ÖLFLEX® HEAT 125 MC - halogen free power and control cable with DNV GL certificate, special fire performance, IEC 60332-3, suitable for +125°C

CPR: www.lappkabel.com/cpr

DNV GL approved



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 125 MC 450/750 V

가

가

, , , , 가

:- (IEC 60754-1)- 가 (IEC 60754-2)- (IEC 61034-2)- (IEC 60332-1-2,NF
C 32-070 (C1) NF-F 16-101 (Class C))- (EN 50305)
IEC 60332-3-22, IEC 60332-3-24 IEC 60332-3-25 ()
acc. IEC 60227-1 (ST9) EN 50264-1 (EM104)
ISO 4892-2 UV-
EN 50396

DNV GL approved
EN 50525-3-21 EN 50525-3-41

가

: 가 ,

ETIM 5:

ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

: 5 : VDE 0293-308 . T9
6 :

: IEC 60228/VDE 0295 class 5

: : 15 x
: 4 x

: U0/U = 450/750 V AC 1.5mm² 0.6/1kV

: 4000 V

: G = GN/YE
X = GN/YE

: : -35 °C~+120 °C
: -55°C ~ +125°C

(24.04.2024)

ÖLFLEX® HEAT 125 MC 450/750 V

(3000h): +145°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: ≤ 30 kg or ≤ 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

ÖLFLEX® HEAT 125 MC 450/750 V

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 125 MC 450/750 V				
1024323	2 X 1.5	7.6	29	71
1024324	3 G 1.5	8.3	43	96
1024366	3 X 1.5	8.3	43.2	115.91
1024325	4 G 1.5	9.0	58	123
1024367	4 X 1.5	9.0	57.6	141.32
1024326	5 G 1.5	10.1	72	156
1024327	7 G 1.5	11.2	101	224
1024328	12 G 1.5	15.1	173	316
1024333	2 X 2.5	9.0	48	102
1024334	3 G 2.5	9.8	72	145
1024335	4 G 2.5	10.8	96	189
1024336	5 G 2.5	11.9	120	235
1024337	7 G 2.5	13.2	168	344
1024339	2 X 4.0	10.6	76.8	193.5
1024340	3 G 4.0	11.4	115	239.73
1024341	4 G 4.0	12.7	154	276
1024342	5 G 4.0	14.0	192	334
1024345	3 G 6.0	12.7	172.8	319.73
1024346	4 G 6.0	14.1	230	341
1024347	5 G 6.0	15.8	288	431
1024351	4 G 10.0	17.9	384	675.1
1024352	5 G 10.0	19.9	480	831.57
1024357	4 G 16.0	20.7	614	1,005.56
1024358	5 G 16.0	23.0	768	1,240.19