

## X05V-K with twin colour helix insulation

X05V-K, , PVC, 300/500 V, class 5, , ,

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)  
PVC



: IEC 60332-1-2  
: d1 = 18 mm; d2 = 200 mm; b = 85 mm

EN 50525-2-31

5(IEC 60228 ) 가 가  
: PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000993
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC000993
	ETIM 6.0 Class :
:	VDE 0295 5/ IEC 60228 5
	가 가



# X05V-K with twin colour helix insulation

:	4 x (OD) H05V-K	; 2 x OD
:	U0/U: 300/500 V	
:	2000 V	
:	VDE 0298 4	
:	EN 50565-1/ VDE 0298-565-1	
:	: -40°C +70°C	

가 가 ( . ) 가 .  
 ,  
 가 VAT 가 가 .

# X05V-K with twin colour helix insulation

		(mm <sup>2</sup> )	(mm)	m/	m/box	(kg/km)	(kg/km)
4512261S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512261K	/	0.5	2.1 - 2.5	-	4000	4.8	9
4512921S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512211S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512231S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512241S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512251S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512271S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512291S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512311S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512371S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512381S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512391S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512401S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512421S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512441S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512461S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512341S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512221S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512281S	/	0.5	2.1 - 2.5	250	-	4.8	9
4512301S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512321S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512351S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512431S	=	0.5	2.1 - 2.5	250	-	4.8	9
4512451S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512471S	-	0.5	2.1 - 2.5	250	-	4.8	9
4512262S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512922S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512202S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512212S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512232S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512242S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512252S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512252K	/	0.75	2.2 - 2.7	-	4000	7.2	12

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# X05V-K with twin colour helix insulation

		(mm <sup>2</sup> )	(mm)	m/	m/box	(kg/km)	(kg/km)
4512272S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512292S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512312S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512332S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512372S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512382S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512392S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512402S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512412S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512422S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512442S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512462S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512342S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512222S	/	0.75	2.2 - 2.7	250	-	7.2	12
4512302S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512322S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512352S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512432S	=	0.75	2.2 - 2.7	250	-	7.2	12
4512452S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512472S	-	0.75	2.2 - 2.7	250	-	7.2	12
4512263S	/	1	2.4 - 2.8	250	-	9.6	15
4512923S	/	1	2.4 - 2.8	250	-	9.6	15
4512203S	/	1	2.4 - 2.8	250	-	9.6	15
4512213S	/	1	2.4 - 2.8	250	-	9.6	15
4512233S	/	1	2.4 - 2.8	250	-	9.6	15
4512243S	/	1	2.4 - 2.8	250	-	9.6	15
4512253S	/	1	2.4 - 2.8	250	-	9.6	15
4512273S	/	1	2.4 - 2.8	250	-	9.6	15
4512293S	/	1	2.4 - 2.8	250	-	9.6	15
4512313S	-	1	2.4 - 2.8	250	-	9.6	15
4512333S	-	1	2.4 - 2.8	250	-	9.6	15
4512363S	-	1	2.4 - 2.8	250	-	9.6	15
4512373S	-	1	2.4 - 2.8	250	-	9.6	15
4512383S	-	1	2.4 - 2.8	250	-	9.6	15

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## X05V-K with twin colour helix insulation

		(mm <sup>2</sup> )	(mm)	m/	m/box	(kg/km)	(kg/km)
4512393S	-	1	2.4 - 2.8	250	-	9.6	15
4512393K	-	1	2.4 - 2.8	-	2000	9.6	15
4512403S	-	1	2.4 - 2.8	250	-	9.6	15
4512413S	-	1	2.4 - 2.8	250	-	9.6	15
4512423S	-	1	2.4 - 2.8	250	-	9.6	15
4512423K	-	1	2.4 - 2.8	-	2000	9.6	15
4512443S	-	1	2.4 - 2.8	250	-	9.6	15
4512463S	-	1	2.4 - 2.8	250	-	9.6	15
4512343S	-	1	2.4 - 2.8	250	-	9.6	15
4512223S	/	1	2.4 - 2.8	250	-	9.6	15
4512283S	/	1	2.4 - 2.8	250	-	9.6	15
4512303S	-	1	2.4 - 2.8	250	-	9.6	15
4512323S	-	1	2.4 - 2.8	250	-	9.6	15
4512353S	-	1	2.4 - 2.8	250	-	9.6	15
4512433S	=	1	2.4 - 2.8	250	-	9.6	15
4512453S	-	1	2.4 - 2.8	250	-	9.6	15
4512473S	-	1	2.4 - 2.8	250	-	9.6	15

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## X05V-K with twin colour helix insulation



(23.04.2024)