

# ÖLFLEX® CRANE CF

가

ÖLFLEX® CRANE CF -  
ø/U: 300/500V

/

, U

EMC-



가

(12.05.2024)

# ÖLFLEX® CRANE CF

ÖLFLEX® CRANE

ÖLFLEX(R) LIFT

A3

50m

가

: IEC 60332-1-2

VDE 0250(NGFLGÖU)

:  
:  
,  
:  
-  
-  
-  
:

ETIM 5:

ETIM 5.0 Class-ID: EC000825  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000825  
ETIM 6.0 Class :

:

5 : VDE 0293-308

T9

6 :

:

VDE 0295/IEC 60228

25 mm<sup>2</sup> : , class 6

35 mm<sup>2</sup> : , class 5

:

: 10 x

: 4 x

:

U0/U: 300/500 V

:

2000 V

:

G = GN/YE

X = GN/YE

:

: -25°C ~ +90°C

: -40°C ~ +90°C

, 가 가 . ( . ) 가 .

[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(12.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® CRANE CF

	(CORE) / (mm <sup>2</sup> )	, x (mm)	(kg/km)	(kg/km)
ÖLFLEX® CRANE CF				
0041075	4.0 G 1.5	18.5 x 6.5	79	220
0041076	8.0 G 1.5	36.0 x 6.5	155	470
0041077	12.0 G 1.5	54.5 x 7.1	238	745
0041078	4.0 G 2.5	22.8 x 7.7	141	320

(12.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16