

ÖLFLEX® HEAT 205 MC

FEP

ÖLFLEX® HEAT 205 MC - FEP

-100°C ~ +205°C

Good chemical resistance please see Appendix T1



(24.04.2024)

ÖLFLEX® HEAT 205 MC



가

가

-
-
-
-
-
-가
-
-

,

FEP ÖLFLEX® HEAT 205

- , , , ,
-
-
-
-
-
-
-
-
-

FEP-

FEP- ,

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

:

5 : VDE 0293-308 -
7 : ÖLFLEX® - , T7

:

VDE 0295, Class 5 / IEC 60228 Class 5 가

(24.04.2024)

ÖLFLEX® HEAT 205 MC

(0.5mm²)

: : 15 x
: 4 x
: U0/U: 300/500 V
: 2500 V
: G = GN/YE
: X = GN/YE
: : -100°C ~ +205°C

가 가 () 가
: www.lappkabel.de/en/cable-standradlengths
30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® HEAT 205 MC

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 205 MC				
0091200	2 X 0.25	3.1	5	17.2
0091201	3 G 0.25	3.3	7.5	22.2
00912023	4 G 0.25	3.6	10	27.5
0091210	2 X 0.5	3.8	9.8	21.6
0091211	3 G 0.5	4	14.7	32.8
00912123	4 G 0.5	4.4	19.6	44.4
0091220	2 X 0.75	4.2	14.4	31.5
0091221	3 G 0.75	4.6	21.6	46.1
00912223	4 G 0.75	4.9	29	57.9
0091230	2 X 1.0	4.5	19	41.6
0091231	3 G 1.0	4.8	29	55.6
00912323	4 G 1.0	5.3	38	70
0091100	3 G 1.5	5.6	43	70
00911033	4 G 1.5	6.1	58	98
00911013	5 G 1.5	6.8	72	117
0091102	7 G 1.5	7.4	101	184
0091236	3 G 2.5	6.6	72	86
00912353	4 G 2.5	7.3	96	115
00912373	5 G 2.5	8.2	120	144
00912423	4 G 4.0	8.7	154	180
00912433	5 G 4.0	9.6	192	225

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16