

ÖLFLEX® HEAT 1565 MC

-195°C +400°C

ÖLFLEX® HEAT 1565 MC - Glass fibre insulated power cable for use in blast furnaces, glassworks, motor construction etc. at ambient temperatures up to +400 °C (short term +1565°C)

: +1565 °C



(23.04.2024)

ÖLFLEX® HEAT 1565 MC

MICA

: MICA , 가 ,

ETIM 5: ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6: ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

: 2- :
4- :
:
:
5 x
U0/U: 300/500 V
2200 V
-195 °C~ +400 °C
()
: +1565 °C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg, . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



ÖLFLEX® HEAT 1565 MC

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 1565 MC				
30020808	2 x 0.5	7	9.6	48
30020809	2 x 0.75	7.4	14.4	66
30016609	2 x 1.0	7.7	19.2	74
30016606	4 x 1.0	8.9	38.4	123
30016603	2 x 1.5	8.2	28.8	87
30016600	4 x 1.5	9.5	57.6	148
30020810	2 x 2.5	9.7	48	114
30020811	2 x 4.0	11.2	76.8	161

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16