

ÖLFLEX® LIFT F

PVC FLAT

ÖLFLEX® LIFT F - / PVC , U
ø/U: 300/500V, H07VVH6-F / H05VVH6-F



가

VDE , 35m 1.6m/s 가 .
ÖLFLEX® CRANE ÖLFLEX(R) LIFT A3

: IEC 60332-1-2

Based on EN 50214/ VDE 0283-2

: PVC
PVC-

(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16

ÖLFLEX® LIFT F

ETIM 5:	ETIM 5.0 Class-ID: EC000825 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000825 ETIM 6.0 Class :
:	5 : VDE 0293-308 . T9
:	6 : U0/U 300/500 V , VDE 0295 5 IEC 60228 Cl. 5 가
:	U0/U 450/750 V , VDE 0295 6 IEC 60228 6 (10 mm ² :
:	/ 5)
:	: 10 x
:	1.0 mm ² : U0/U: 300/500 V
:	.5 mm ² : U0/U: 450/750 V
:	3000 V
:	G = GN/YE
:	X = GN/YE
:	:
:	0°C ~ +70°C (1.0 mm ²)
:	-15 °C ~ +70°C (1.5 mm ²)

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

	(CORE) / (mm ²)	, x (mm)	(kg/km)	(kg/km)
ÖLFLEX® LIFT F				
U0/U: 300/500 V, : 0°C ~ +70°C				
0042020	12.0 G 1.0	36 x 4.7	115	392
0042021	16.0 G 1.0	48.5 x 4.7	153.6	521
0042022	20.0 G 1.0	59 x 4.7	192	645
0042023	24.0 G 1.0	71.5 x 4.7	230	772
U0/U: 450/750 V, : -15°C ~ +70°C				
00420013	4.0 G 1.5	15.5 x 5.2	57.6	132
00420023	5.0 G 1.5	19.7 x 5.2	72	170
0042003	7.0 G 1.5	27 x 5.2	100.8	236
0042004	8.0 G 1.5	29 x 5.2	115	266
0042005	10.0 G 1.5	36.5 x 5.2	144	333
0042006	12.0 G 1.5	42 x 5.2	172.8	422
00420073	4.0 G 2.5	19 x 5.9	96	206
00420083	5.0 G 2.5	24 x 5.9	120	257
0042009	7.0 G 2.5	32.5 x 5.9	168	345
0042010	8.0 G 2.5	35 x 5.9	192	390
0042050	12.0 G 2.5	52.5 x 5.9	288	580
00420113	4.0 G 4.0	21 x 6.8	153.6	343
0042012	7.0 G 4.0	38 x 6.8	268.8	589
00420133	4.0 G 6.0	24 x 7.3	230	425
00420143	4.0 G 10.0	30.5 x 9.5	384	709
00420153	4.0 G 16.0	35 x 10.8	614	1015
00420163	4.0 G 25.0	42 x 13	960	1366

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16