

# ÖLFLEX® HEAT 1565 SC

-195°C +400°C

ÖLFLEX® HEAT 1565 SC - Glass fibre insulated single core for use in blast furnaces, glassworks, motor construction etc. at ambient temperatures up to +400°C (short term +1565°C)

: +1565 °C



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® HEAT 1565 SC

:

ETIM 5: ETIM 5.0 Class-ID: EC000993  
ETIM 5.0 Class :  
ETIM 6: ETIM 6.0 Class-ID: EC000993  
ETIM 6.0 Class :  
:  
: : 5 x  
:  
: U0/U: 300/500 V  
:  
: 2200 V  
:  
: -195 °C~ +400 °C  
( )  
: +1565 °C

가 가 ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .



# ÖLFLEX® HEAT 1565 SC

	(mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT SC 1565				
3020780	0.75	2.9	7.2	15.9
3020781	1.0	3	9.6	18.8
3013234	1.5	3.3	14.4	24.3
3020782	2.5	3.8	24	35
3018942	4.0	4.8	38.4	56
3020783	6.0	5.6	57.6	86.4
3016697	10.0	6.2	96	123
3016698	16.0	7.9	153.6	202.5
3016699	25.0	9.2	240	295.1
3016771	35.0	10.6	336	403.9
3017861	50.0	12.2	480	545

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16