

ÖLFLEX® CRANE PUR

ÖLFLEX® CRANE PUR -
ø/U: 0.6/1kV

/

가 ,U

, -40°C



(28.04.2024)

ÖLFLEX® CRANE PUR



, 가
가

In dry or damp interiors, outdoors and in industrial water

ÖLFLEX® CRANE

ÖLFLEX(R) LIFT

A3

ÖLFLEX® CRANE

T4

; ÖLFLEX(R) LIFT

T5

(IEC 60332-1-2)

EN 60811-404

: TPE

: PUR

ETIM 5:

ETIM 5.0 Class-ID: EC000057

ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057

ETIM 6.0 Class :

:

5 : VDE 0293-308

T9

6 :

VDE 0295 class 6, IEC 60228 class 6

가

:

: 7.5 x

:

U0/U: 600/1000 V

:

4000 V

:

G = GN/YE

(28.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CRANE PUR

X = GN/YE

VDE 298 4

: -40°C ~ +80°C

가 가 . (.) 가 .
 www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(28.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® CRANE PUR

	(CORE) /	(mm ²)	(mm)	(N)	(kg/km)	(kg/km)
ÖLFLEX® CRANE PUR						
0045207	4 G 1.5		10.9	500	57.6	169
0045209	5 G 1.5		11.6	1000	72	197
0045210	7 G 1.5		12.9	2500	100.8	239
0045211	12 G 1.5		17.6	2500	172.8	401
0045212	18 G 1.5		17.5	2500	259.2	507
0045213	24 G 1.5		20.7	2500	345.6	673
0045215	30 G 1.5		28.9	3000	432	1100
0045214	36 G 1.5		31.4	3000	518.4	1350
0045216	4 G 2.5		12.2	500	96	227
0045218	5 G 2.5		13.2	2000	120	274
0045220	7 G 2.5		15.4	3000	168	358
0045221	12 G 2.5		21.6	3000	288	619
0045222	18 G 2.5		21.5	3000	432	793
0045223	24 G 2.5		25.5	3000	576	1123
0045224	30 G 2.5		34.7	3000	720	1641
0045225	4 G 4.0		14.3	1000	153.6	341
0045227	5 G 4.0		15.5	2000	192	411
0045228	4 G 6.0		16.6	1500	230.4	457
0045229	5 G 6.0		17.7	2000	288	538
0045235	7 G 6.0		20.2	2500	403	750
0045230	4 G 10.0		19.2	2000	384	674
0045237	5 G 10.0		21.6	2500	480	825
0045231	4 G 16.0		22.2	2500	614.4	966
0045238	5 G 16.0		25.6	3500	768	1222
0045232	4 G 25.0		27.6	3500	960	1506
0045233	4 G 35.0		31	4500	1344	2004
0045234	4 G 50.0		36.1	6000	1920	2838
0045240	3x25+3G6		25.7	2000	892.8	1380
0045241	3x35+3G6		27.6	2500	1,180.8	1695
0045242	3x50+3G10		32.1	3500	1728	2307

(28.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16