



ÖLFLEX® HEAT 650 SC

-50°C ~ +700°C

ÖLFLEX® HEAT 650 SC - +650°C , ,



가

, , , 가 ,

ÖLFLEX® HEAT 1565 SC 가 700°C

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 650 SC

: 가

ETIM 5: ETIM 5.0 Class-ID: EC000993
ETIM 5.0 Class :

ETIM 6: ETIM 6.0 Class-ID: EC000993
ETIM 6.0 Class :

:

: 5 x

: U0/U: 300/500 V

: 1800 V

: -50°C ~ +700°C

: , 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths

: 30 kg, . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



ÖLFLEX® HEAT 650 SC

	(mm ²)	(mm)	(kg/km)	(kg/km)
1232650	0.5	2.4	4.8	13
1232651	0.75	2.5	7.6	15
1232652	1.0	2.9	9.7	17
1232653	1.5	3	14.8	23
1232654	2.5	3.5	23.5	34
1232655	4.0	3.9	38.6	54
1232656	6.0	4.6	57.9	84
1232657	10.0	7.8	96.5	120
1232658	16.0	8.2	152	199
1232659	25.0	9.8	236.4	300
1232660	35.0	10.6	332.8	399
1232661	50.0	11.2	481.1	540

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16