

# ÖLFLEX® CRANE VS (N)SHTÖU

ÖLFLEX® CRANE VS(N)SHTÖU -  
ø/U: 0.6/1kV

/

가 ,U



가

(23.04.2024)

# ÖLFLEX® CRANE VS (N)SHTÖU

In dry or damp interiors, outdoors and in industrial water

ÖLFLEX® CRANE

ÖLFLEX(R) LIFT

A3

ÖLFLEX® CRANE

T5

T4

; ÖLFLEX(R) LIFT

: IEC 60332-1-2  
EN 60811-404

VDE 0250-814(NSHTÖU)

: 3GI3

: , type 5GM5

ETIM 5:

ETIM 5.0 Class-ID: EC000057  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057  
ETIM 6.0 Class :

:

5 : VDE 0293-308

T9

6 :

:

VDE 0295 5/ IEC 60228 5

가 가

:

: 7.5 x

:

U0/U: 600/1000 V

:

3000 V

:

G = GN/YE

X = GN/YE

:

VDE 298 4

:

: -25°C ~ +80°C

: www.lappkabel.de/en/cable-standradlengths  
30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m).

(23.04.2024)



## ÖLFLEX® CRANE VS (N)SHTÖU

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® CRANE VS (N)SHTÖU

	(CORE) /	(mm <sup>2</sup> )	(mm)	(N)	(kg/km)	(kg/km)
ÖLFLEX® CRANE VS (N)SHTÖU						
0044008	7 G 1.5		18.8	2000	100.8	430
0044009	12 G 1.5		25.3	2000	172.8	820
0044010	18 G 1.5		25.3	2000	259.2	930
0044011	24 G 1.5		30.1	2000	345.6	1260
0044036	36 G 1.5		34	2000	518.4	1650
0044015	7 G 2.5		21.6	2000	168	630
0044016	12 G 2.5		29.4	2000	288	1150
00440333	5 G 4.0		19.6	2000	192	510
00440223	4 G 10.0		23.4	2000	384	830
00440233	4 G 16.0		25.5	2000	614.4	1170
00440323	5 G 16.0		27.5	2400	768	1400
00440243	4 G 25.0		32.6	3000	960	1850
00440253	4 G 35.0		34.8	4000	1344	2250
00440263	4 G 50.0		40.6	6000	1920	3200
00440283	4 G 70.0		44.8	8000	2688	4200
00440293	4 G 95.0		51.2	11000	3648	5550

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16