

ÖLFLEX® CRANE

가

ÖLFLEX® CRANE -
0/U: 300/500V

,

/

,

,U



가

24

(

)

가

Use outdoors and in industrial water

(23.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16

ÖLFLEX® CRANE

ÖLFLEX® CRANE

ÖLFLEX(R) LIFT

A3

, ÖLFLEX® FD

;

T3

: IEC 60332-1-2

가

Refer to the article table for the tensile strength of the cable

가

VDE 0250

:

: , type EM2

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

:

5 : VDE 0293-308

T9

6 :

:

0.15 mm at 1.0 mm²

:

: 12.5 x

: 6 x

:

U0/U: 300/500 V

:

3000 V

:

G = GN/YE

X = GN/YE

:

: -25°C ~ +80°C

: -40°C +80°C

, 가 가 . (.) 가 .

www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CRANE

	(CORE) /	(mm ²)	(mm)	(N)	(kg/km)	(kg/km)
ÖLFLEX® CRANE						
0039001	2.0 X 1.0		7.4	300	19.2	89
0039002	3.0 G 1.0		8.3	300	28.8	106
00390033	4.0 G 1.0		8.9	300	38.4	127
00390043	5.0 G 1.0		10.4	300	48	149
0039107	7.0 G 1.0		12.9	300	67.2	206
0039109	9.0 G 1.0		14.4	300	86.4	281
0039054	12.0 G 1.0		18.5	360	115.2	422
0039055	18.0 G 1.0		19.2	540	172.8	451
0039056	24.0 G 1.0		22.1	720	230.4	646
0039057	36.0 G 1.0		26.1	1080	345.6	863
0039017	2.0 X 1.5		8	300	28.8	108
0039018	3.0 G 1.5		8.7	300	43.2	128
00390193	4.0 G 1.5		9.9	300	57.6	158
00390203	5.0 G 1.5		10.9	300	72	188
0039061	7.0 G 1.5		14	315	100.8	260
0039208	8.0 G 1.5		15.2	360	115.2	300
0039209	9.0 G 1.5		15.9	405	129.6	375
0039210	10.0 G 1.5		17	450	144	427
0039058	12.0 G 1.5		19.9	540	172.8	557
0039059	18.0 G 1.5		20.9	810	259.2	608
0039060	24.0 G 1.5		23.4	1080	345.6	825
0039034	2.0 X 2.5		9.7	300	48	145
0039035	3.0 G 2.5		10.2	300	72	173
00390363	4.0 G 2.5		11.6	300	96	219
00390373	5.0 G 2.5		12.4	375	120	259
0039307	7.0 G 2.5		16.6	525	168	378
0039309	9.0 G 2.5		18.9	675	216	518
0039312	12.0 G 2.5		23.3	900	288	770
0039316	16.0 G 2.5		22.8	1200	384	749
0039318	18.0 G 2.5		24.4	1350	432	837
0039324	24.0 G 2.5		28.5	1800	576	1184
00390463	4.0 G 4.0		15.2	480	153.6	307
00390473	5.0 G 4.0		16.8	600	192	394

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



ÖLFLEX® CRANE

	(CORE) / (mm ²)	(mm)	(N)	(kg/km)	(kg/km)
00390483	4.0 G 6.0	16.8	720	230.4	409
00390493	5.0 G 6.0	19.2	900	288	528
00390503	4.0 G 10.0	21.8	1200	384	698
00390513	5.0 G 10.0	24.6	1500	480	853
00390523	4.0 G 16.0	25.4	1920	614.4	974
00390533	5.0 G 16.0	28	2400	768	1226

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16