

ÖLFLEX® HEAT 260 GLS

가

PTFE

ÖLFLEX® HEAT 260 GLS - steel-armoured PTFE power cable, for increased mechanical stress, DNV GL certified for ship-building and diesel engines up to +260°C

DNV GL approved



DNV GL certification for use with ship diesel engines

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 260 GLS

-
-
-
-
-
-

CNV GL certificate no. TAE00001JF

PTFE-

가

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	5 : VDE 0293-308 . T9
	7-
	GN/YE, , , , , ,
:	VDE 0295 5/ IEC 60228 5
	가 가
:	:
	5 x
:	U0/U 300/500 V
	GL: 250 V
:	1500 V
:	G = GN/YE
:	X = GN/YE
:	: -190°C ~ +260°C
	GL : +205 °C

가 가 (.) 가 .
: www.lappkabel.de/en/cable-standradlengths
30 kg or 250 m,

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 260 GLS

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® HEAT 260 GLS

	(CORE) /	(mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 260 GLS					
0091120	2 X 1.5		5.7	29	93
0091121	3 G 1.5		6.1	43	102
00911223	4 G 1.5		6.6	58	130
00911233	5 G 1.5		7.3	72	149
0091124	7 G 1.5		8	101	180

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16