

ÖLFLEX® HEAT 105 MC

PVC

ÖLFLEX® HEAT 105 MC - +90°C

H05V2V2-F

PVC

H05V2V2-F

가

가

CPR: www.lappkabel.com/cpr



PVC

(30%)

가

, , , , , 가 ,

가

: IEC 60332-1-2
UV-

In Anlehnung an EN 50525-2-11

(01.05.2024)

ÖLFLEX® HEAT 105 MC

가
: PVC, -
: PVC, , (RAL 9005)

ETIM 5: ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가
ETIM 6: ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :
: 5 : VDE 0293-308 T9
6 : ÖLFLEX® , T7
:
: IEC 60228/VDE 0295 class 5
: : 15 x
: 4 x
: U0/U: 300/500 V
: 2500 V
: G = GN/YE
: X = GN/YE
: : +105 °C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).
가 VAT 가 가 .



ÖLFLEX® HEAT 105 MC

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 105 MC				
0026001	2 X 0.75	6.2	14.4	53
0026002	3 G 0.75	6.5	21.6	62
00260033	4 G 0.75	7.1	28.8	76
00260043	5 G 0.75	8	36	95
0026005	7 G 0.75	9.7	50	113
0026006	2 X 1.0	6.5	19.2	61
0026007	3 G 1.0	6.9	29	74
00260083	4 G 1.0	7.7	38.4	89
00260093	5 G 1.0	8.4	48	110
0026010	7 G 1.0	10.2	67	130
0026011	2 X 1.5	7.5	29	78
0026012	3 G 1.5	8.1	43.2	98
00260133	4 G 1.5	8.9	57.6	122
00260143	5 G 1.5	10	72	144
0026015	7 G 1.5	12.3	101	180

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16