

# ÖLFLEX® HEAT 350 MC

-50 °C +350 °C

ÖLFLEX® HEAT 350 MC - Glass fibre insulated power cable for use in blast furnaces, glassworks, motor construction etc. at ambient temperatures up to +350°C

: 230/400 V



C (>180°C) 가

(30.05.2024)

# ÖLFLEX® HEAT 350 MC

ÖLFLEX® HEAT 1565 MC 가 350

: 가  
:가 , ( )

ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class :
:	VDE 0293-308 , T9
:	VDE 0295 5/ IEC 60228 5 가 가
:	: 6 x
:	U0/U 230/400V
:	1500 V
:	: -50°C ~ +350°C ( )

, 가 가 . ( . ) 가 .  
: [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
30 kg, . (e.g. 1 x 500 m or 5 x 100 m ).  
가 VAT 가 가 .



# ÖLFLEX® HEAT 350 MC

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 350 MC				
0091375	2 X 1.0	6.8	19.2	56
0091376	3 G 1.0	7.4	28.8	70
0091377	4 G 1.0	8.2	38.4	88
0091380	2 X 1.5	7.8	28.8	77
0091381	3 G 1.5	8.4	43.2	93
0091382	4 G 1.5	9.4	57.6	118
0091383	5 G 1.5	10.3	72	140
0091390	3 G 2.5	8.9	72	124
0091391	4 G 2.5	9.8	96	160
0091392	5 G 2.5	10.1	120	194

(30.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16