

# ÖLFLEX® HEAT 350 SC

-50 °C +350 °C

ÖLFLEX® HEAT 350 SC - Glass fibre insulated single core for use in blast furnaces, glassworks, motor construction etc. at ambient temperatures up to +350°C



C (>180°C) 가

ÖLFLEX® HEAT 650 SC    ÖLFLEX® HEAT 1565 SC    가 +350°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® HEAT 350 SC

: 가  
:  
(16 mm<sup>2</sup> 가 )  
:  
가  
:

ETIM 5:	ETIM 5.0 Class-ID: EC000993
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC000993
	ETIM 6.0 Class :
:	VDE 0295 5/ IEC 60228 5
	가 가
:	: 5 x
:	U0/U 230/400V
:	1500 V
:	: -50°C ~ +350°C
	( )

가 가 ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg,  
(e.g. 1 x 500 m or 5 x 100 m ).  
가 VAT 가 가 .



# ÖLFLEX® HEAT 350 SC

	(mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 350 SC				
0091350	0.5	2.5	4.8	13
0091351	0.75	3	7.2	15
0091352	1.0	3.4	9.6	17
0091353	1.5	3.5	14.4	23
0091354	2.5	3.7	24	34
0091355	4.0	4.2	38.4	54
0091356	6.0	6.2	57.6	84
0091357	10.0	7.3	96	120
0091358	16.0	8	153.6	199
0091359	25.0	9.5	240	300
0091360	35.0	10.9	336	399
0091361	50.0	13.2	480	540

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16