

ÖLFLEX® HEAT 180 EWKF

가

ÖLFLEX® HEAT 180 EWKF -
+180°C

- EWKF

가 가

CPR: www.lappkabel.com/cpr



EWKF

가

, 가

SiO₂()

가

가 가

(23.04.2024)

ÖLFLEX® HEAT 180 EWKF

-
-
- /
- 가
-
-
-
-

EWKF:

가 (IEC 60754-1), UV- 가 (IEC 60754-2), (IEC 60332-1-2)
가 , , , +100°C 가

In Anlehnung an EN 50525-2-83

: EWKF

: EWKF, ,

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	VDE 0293-308 , T9
	6 :
:	VDE 0295 5/ IEC 60228 5
	가 가
:	: 15 x
	: 4 x
:	U0/U: 300/500 V
:	2000 V
:	G = GN/YE
	X = GN/YE
:	-60°C ~ +180°C
	()

, 가 가 . (.) 가 .
: www.lappkabel.de/en/cable-standradlengths
30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m).

(23.04.2024)



ÖLFLEX® HEAT 180 EWKF

가 VAT 가 가 .

(23.04.2024)



ÖLFLEX® HEAT 180 EWKF

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 EWKF				
0046500	2 X 0.75	6.4	15	49
0046501	3 G 0.75	6.9	22	60
00465023	4 G 0.75	7.6	29	76
00465033	5 G 0.75	8.5	36	96
0046506	2 X 1.0	6.8	20	56
0046507	3 G 1.0	7.1	29	68
00465083	4 G 1.0	7.9	39	88
00465093	5 G 1.0	8.8	48	110
0046110	7 G 1.0	9.5	67.2	137
0046511	2 X 1.5	8	29	77
0046512	3 G 1.5	8.4	43	94
00465133	4 G 1.5	9.5	58	117
00465143	5 G 1.5	10.4	72	143
0046115	7 G 1.5	11	101	180
0046116	12 G 1.5	14.9	173	319
0046117	16 G 1.5	17.1	230.4	424
0046119	24 G 1.5	21	345.6	637
0046520	2 X 2.5	9.4	48	110
0046521	3 G 2.5	9.8	72	146
00465223	4 G 2.5	11.1	96	181
00465233	5 G 2.5	11.9	120	222
0046131	3 G 4.0	11.5	114	213
00461323	4 G 4.0	12.5	152	267
00461333	5 G 4.0	13.9	190	334
0046141	3 G 6.0	13.2	174	297
00461423	4 G 6.0	14.7	232	381
00461433	5 G 6.0	16.5	290	481

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16