

ÖLFLEX® HEAT 260 SC

가

ÖLFLEX® HEAT 260 SC - PTFE

-190°C ~ +260°C

UL AWM Style 11486 (28-12 AWG)



(23.04.2024)

ÖLFLEX® HEAT 260 SC

가

Typical fields of application

- High-frequency engineering
- Control cabinets with high heat generation
- Measuring instruments
- Furnaces and brickworks
- Heating equipment and kitchen appliances
- Electric motor building
- Installations in the chemical industry

(UL): FT2 ()

IEC 60332-1-2 CSA FT1

PTFE ÖLFLEX® HEAT 260

- , , , , ,
-
-
-
-
-
-
-
-
-
-

()

28-12 AWG: UL AWM Style 11486 according to UL 758 (File No E63634) & cRU AWM I A/B according to CSA C22.2 No 210 (File No E63634)

AWG

PTFE

PTFE = Polytetrafluoroethylene

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

AWG : 7, 19 37

:

: 4 x

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 260 SC

: U0/U: 300/500 V
: 3400 V
: : -190°C ~ +260°C
UL/CSA: up to +200°C

: 100m , 가 가 . (.) 가 .
가 가 .
가 가 가 가 .
가 VAT 가 가 .
가 가



ÖLFLEX® HEAT 260 SC

	AWG No. and wire number	(mm)		(kg/km)	(kg/km)
ÖLFLEX® HEAT 260 SC					
0094000	28 (7)	0.9	/	0.9	2
0094001	28 (7)	0.9		0.9	2
0094002	28 (7)	0.9		0.9	2
0094003	28 (7)	0.9		0.9	2
0094005	28 (7)	0.9		0.9	2
0094006	28 (7)	0.9		0.9	2
0094007	28 (7)	0.9		0.9	2
0094009	28 (7)	0.9		0.9	2
0094104	28 (7)	0.9		0.9	2
0094105	28 (7)	0.9		0.9	2
0094106	28 (7)	0.9		0.9	2
0095001	26 (7)	1.0		1.4	2.7
0095002	26 (7)	1.0		1.4	2.7
0095006	26 (7)	1.0		1.4	2.7
0095007	26 (7)	1.0		1.4	2.7
0095009	26 (7)	1.0		1.4	2.7
0095104	26 (7)	1.0		1.4	2.7
0095105	26 (7)	1.0		1.4	2.7
0095106	26 (7)	1.0		1.4	2.7
0096000	26 (19)	1.0	/	1.5	2.9
0096001	26 (19)	1.0		1.5	2.9
0096006	26 (19)	1.0		1.5	2.9
0106011	26 (19)	1.0		1.5	2.9
0096104	26 (19)	1.0		1.5	2.9
0097001	24 (7)	1.15		2.2	3.8
0097002	24 (7)	1.15		2.2	3.8
0097003	24 (7)	1.15		2.2	3.8
0097104	24 (7)	1.15		2.2	3.8
0097105	24 (7)	1.15		2.2	3.8
0098000	24 (19)	1.15	/	2.3	4
0098001	24 (19)	1.15		2.3	4
0098002	24 (19)	1.15		2.3	4
0098003	24 (19)	1.15		2.3	4

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 260 SC

	AWG No. and wire number	(mm)		(kg/km)	(kg/km)
0098006	24 (19)	1.15		2.3	4
0098104	24 (19)	1.15		2.3	4
0098105	24 (19)	1.15		2.3	4
0098106	24 (19)	1.15		2.3	4
0099001	22 (7)	1.3		3.4	5.4
0099002	22 (7)	1.3		3.4	5.4
0099003	22 (7)	1.3		3.4	5.4
0099005	22 (7)	1.3		3.4	5.4
0099006	22 (7)	1.3		3.4	5.4
0099007	22 (7)	1.3		3.4	5.4
0099104	22 (7)	1.3		3.4	5.4
0099105	22 (7)	1.3		3.4	5.4
0100001	22 (19)	1.3		3.7	5.7
0100002	22 (19)	1.3		3.7	5.7
0100003	22 (19)	1.3		3.7	5.7
0100005	22 (19)	1.3		3.7	5.7
0100009	22 (19)	1.3		3.7	5.7
0100104	22 (19)	1.3		3.7	5.7
0100105	22 (19)	1.3		3.7	5.7
0101001	20 (7)	1.5		5.4	7.7
0101002	20 (7)	1.5		5.4	7.7
0101003	20 (7)	1.5		5.4	7.7
0101006	20 (7)	1.5		5.4	7.7
0101104	20 (7)	1.5		5.4	7.7
0101105	20 (7)	1.5		5.4	7.7
0102001	20 (19)	1.5		5.9	8.2
0102002	20 (19)	1.5		5.9	8.2
0102003	20 (19)	1.5		5.9	8.2
0102005	20 (19)	1.5		5.9	8.2
0102006	20 (19)	1.5		5.9	8.2
0102007	20 (19)	1.5		5.9	8.2
0102009	20 (19)	1.5		5.9	8.2
0102104	20 (19)	1.5		5.9	8.2
0102105	20 (19)	1.5		5.9	8.2
0102106	20 (19)	1.5		5.9	8.2

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 260 SC

	AWG No. and wire number	(mm)		(kg/km)	(kg/km)
0103001	18 (7)	1.75		8.6	12
0102000	20 (19)	1.5	/	5.9	8.2
0103104	18 (7)	1.75		8.6	12
0104000	18 (19)	1.75	/	9.3	12
0104001	18 (19)	1.75		9.3	12
0104002	18 (19)	1.75		9.3	12
0104003	18 (19)	1.75		9.3	12
0104005	18 (19)	1.75		9.3	12
0104006	18 (19)	1.75		9.3	12
0104007	18 (19)	1.75		9.3	12
0104009	18 (19)	1.75		9.3	12
0104104	18 (19)	1.75		9.3	12
0104105	18 (19)	1.75		9.3	12
0105000	16 (19)	2.05	/	11.8	16
0105001	16 (19)	2.05		11.8	16
0105002	16 (19)	2.05		11.8	16
0105003	16 (19)	2.05		11.8	16
0105005	16 (19)	2.05		11.8	16
0105006	16 (19)	2.05		11.8	16
0105007	16 (19)	2.05		11.8	16
0105009	16 (19)	2.05		11.8	16
0105104	16 (19)	2.05		11.8	16
0105105	16 (19)	2.05		11.8	16
0106000	14 (19)	2.45	/	18.7	23
0106001	14 (19)	2.4		18.7	23
0106002	14 (19)	2.4		18.7	23
0106003	14 (19)	2.4		18.7	23
0106005	14 (19)	2.4		18.7	23
0106006	14 (19)	2.4		18.7	23
0106104	14 (19)	2.4		18.7	23
0106105	14 (19)	2.4		18.7	23
0106106	14 (19)	2.4		18.7	23
0107000	12 (19)	3.1	/	29.6	35
0107001	12 (19)	3.1		29.6	35
0107002	12 (19)	3.1		29.6	35

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 260 SC

	AWG No. and wire number	(mm)		(kg/km)	(kg/km)
0107003	12 (19)	3.1		29.6	35
0107005	12 (19)	3.1		29.6	35
0107006	12 (19)	3.1		29.6	35
0107009	12 (19)	3.1		29.6	35
0107105	12 (19)	3.1		29.6	35
0108000	10 (37)	3.4	/	45.6	51
0108001	10 (37)	3.4		45.6	51
0108002	10 (37)	3.4		45.6	51
0108104	10 (37)	3.4		45.6	51
0108105	10 (37)	3.4		45.6	51

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16