

ÖLFLEX® HEAT 180 C MS

(AWM)

ÖLFLEX® HEAT 180 C MS -
+180°C

, UL/CSA AWM,

MS =
UL AWM Style 4476 (150 °C/600 V)
CPR: www.lappkabel.com/cpr



FT-1

/

(23.04.2024)

ÖLFLEX® HEAT 180 C MS

- ,
-
- /
- 가
-
-
-

(IEC 60754-1), 가 (IEC 60754-2)
acc. to IEC 60332-1-2, , CSA FT 1
가 UV-
가 , , , +100°C 가

UL AWM 4476 cUL AWM II A/B
B,
UL File No. E63634

-
-
,

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	VDE 0293-308 , T9
	6 :
:	IEC 60228/VDE 0295 class 5
	AWG US T16
:	: 20 x
	: 6 x
:	U0/U: 300/500 V
	UL: 600 V
:	2000 V
:	G = GN/YE
	X = GN/YE
:	VDE : -60°C ~ +180°C



ÖLFLEX® HEAT 180 C MS

UL : +150°C
()

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)



ÖLFLEX® HEAT 180 C MS

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 C MS				
0046701	3 G 0.5	8.6	43.4	100
0046702	4 G 0.5	9.3	55.4	122
0046703	5 G 0.5	10	60.2	137
0046708	2 X 1.0	9	48.2	104
0046709	3 G 1.0	9.5	65	131
0046710	4 G 1.0	10.2	74.6	152
0046711	5 G 1.0	11	91.5	181
0046712	7 G 1.0	11.9	117.9	228
0046716	2 X 1.5	9.6	65	126
0046717	3 G 1.5	10.1	79.4	152
0046718	4 G 1.5	10.9	101.1	186
0046719	5 G 1.5	11.8	122.7	222
0046720	7 G 1.5	12.8	158.7	281
0046721	12 G 1.5	16.9	245.2	431
0046723	18 G 1.5	19.6	346.1	600
0046724	25 G 1.5	23.9	495.7	833
0046728	3 G 2.5	11	115.5	197
0046729	4 G 2.5	11.9	146.7	244
0046730	5 G 2.5	12.9	177.9	291
0046734	3 G 4.0	12.3	165.9	261
0046735	4 G 4.0	13.4	211.5	325
0046736	5 G 4.0	14.9	257.2	389
0046740	4 G 6.0	17.2	302.8	482
0046741	5 G 6.0	18.7	367.6	580
0046742	4 G 10.0	22.8	508.4	802

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16