

# ÖLFLEX® HEAT 180 MS

(AWM )

ÖLFLEX® HEAT 180 MS -

, UL/CSA AWM, +180°C

MS =

UL AWM Style 4476 (150 °C/600 V)

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



FT-1

SiO<sub>2</sub>( )

가

/

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® HEAT 180 MS

-  
-  
-  
-  
-  
-  
-

/  
가

(IEC 60754-1), 가 (IEC 60754-2)  
acc. to IEC 60332-1-2, , CSA FT 1  
가 UV-

가 , , , +100°C 가

UL AWM 4476 cUL AWM II A/B  
B,  
UL File No. E63634

-  
,

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	VDE 0293-308 , T9
	6 :
:	IEC 60228/VDE 0295 class 5
	AWG US T16
:	: 15 x
	: 4 x
:	U0/U: 300/500 V
	UL: 600 V
:	2000 V
:	G = GN/YE
	X = GN/YE
:	VDE : -60°C ~ +180°C
	UL : +150°C
	( )



# ÖLFLEX® HEAT 180 MS

가 가 . ( . ) 가 .  
 : [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 가 VAT 가 가 .

# ÖLFLEX® HEAT 180 MS

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 MS				
0046600	2 X 0.5	7.4	9.8	72
0046601	3 G 0.5	7.8	14.7	83
00466023	4 G 0.5	8.5	19.6	99
00466033	5 G 0.5	9.2	24.5	119
0046604	7 G 0.5	9.9	34.3	142
0046612	2 X 1.0	8.2	19.2	93
0046613	3 G 1.0	8.7	28.8	110
00466143	4 G 1.0	9.4	38.4	133
00466153	5 G 1.0	10.3	48	160
0046616	7 G 1.0	11.1	67.2	195
0046617	12 G 1.0	14.9	115.2	345
0046618	2 X 1.5	8.8	28.8	113
0046619	3 G 1.5	9.3	43.2	135
00466203	4 G 1.5	10.1	57.6	165
00466213	5 G 1.5	11.1	72	200
0046622	7 G 1.5	12	100.8	246
0046623	12 G 1.5	16.1	172.8	437
0046625	18 G 1.5	18.8	259.2	613
0046626	25 G 1.5	22.9	360	904
0046628	2 X 2.5	9.6	48	146
0046629	3 G 2.5	10.2	72	178
00466303	4 G 2.5	11.1	96	220
00466313	5 G 2.5	12.2	120	269
0046633	3 G 4.0	11.5	115.2	246
00466343	4 G 4.0	12.6	153.6	307
00466353	5 G 4.0	14.2	192	389
0046636	3 G 6.0	14.9	172.8	396
00466373	4 G 6.0	16.4	230.4	495
00466383	5 G 6.0	18	288	608

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16