

# ÖLFLEX® HEAT 180 EWKF C

가 가

ÖLFLEX® HEAT 180 EWKF C -  
+180°C

- EWKF

EMC

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



EWKF 가 , 가

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® HEAT 180 EWKF C

가 가

- ,  
-  
- /  
- 가  
-  
-  
-

EWKF:

가 (IEC 60754-1), UV- 가 (IEC 60754-2), (IEC 60332-1-2)  
가 , , +100°C 가

-  
-

: EWKF, ,

ETIM 5:

ETIM 5.0 Class-ID: EC001578  
ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578  
ETIM 6.0 Class :

: 5 : VDE 0293-308 . T9  
6 :  
: VDE 0295 5/ IEC 60228 5  
가 가  
: : 20 x  
: 6 x  
: U0/U: 300/500 V  
: 2000 V  
: G = GN/YE  
: X = GN/YE  
: -60°C ~ +180°C  
( )

, 가 가 . ( . ) 가 .  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

(23.04.2024)



# ÖLFLEX® HEAT 180 EWKF C

: 30 kg or 250 m, (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(23.04.2024)



# ÖLFLEX® HEAT 180 EWKF C

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 EWKF C				
0046301	2 X 0.75	8.6	37.5	104
0046302	3 G 0.75	8.9	46.1	118
00463033	4 G 0.75	10.2	57.3	152
00463043	5 G 0.75	10.9	67.3	176
0046307	2 X 1.0	9	43	116
0046308	3 G 1.0	9.7	55.7	142
00463093	4 G 1.0	10.9	67.8	175
00463103	5 G 1.0	11.6	80.3	203
0046312	7 G 1.0	12.3	113.9	250
0046313	2 X 1.5	10.8	58	166
0046314	3 G 1.5	11.2	74	188
00463153	4 G 1.5	12	91.4	222
00463163	5 G 1.5	12.8	121.7	273
0046318	7 G 1.5	13.6	157.2	341
0046320	3 G 2.5	12.8	121.2	271
00463213	4 G 2.5	13.9	150.9	328
00463223	5 G 2.5	14.8	180.5	387
00463273	4 G 4.0	16	218	448
00463283	5 G 4.0	17.2	262.9	531
0046330	3 G 6.0	16.4	240.5	489
00463313	4 G 6.0	17.9	304.7	591
00463323	5 G 6.0	19.4	370	706

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16