



ÖLFLEX® HEAT 180 SiF

가

ÖLFLEX® HEAT 180 SiF - +180°C

CPR: www.lappkabel.com/cpr



SiO2() 가

- 가

- /

-
-
-
-
-
-

(23.04.2024)

ÖLFLEX® HEAT 180 SiF

IEC 60754-1

(가)

IEC 60754-2 () , 가

: IEC 60332-1-2

가

+100°C

가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

VDE 0295, Class 5 / IEC 60228 Class 5 가
(0.5mm²)

:

: 6 x

1 , :

3 x

:

U0/U: 300/500 V

:

2000 V

:

-50 °C +180 °C

()

: +200°C

, 가 가 . (.) 가 .

www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

가 가

가 VAT

가 가 .

가

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 180 SiF

	(mm ²)	(mm)		(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 SiF					
0047000	0.25	1.9	/	2.4	5.4
0047001	0.25	1.9		2.4	5.4
0047002	0.25	1.9		2.4	5.4
0047003	0.25	1.9		2.4	5.4
0047005	0.25	1.9		2.4	5.4
0047006	0.25	1.9		2.4	5.4
0047007	0.25	1.9		2.4	5.4
0047008	0.25	1.9		2.4	5.4
0047009	0.25	1.9		2.4	5.4
0047104	0.25	1.9		2.4	5.4
0047105	0.25	1.9		2.4	5.4
0047106	0.25	1.9		2.4	5.4
0048000	0.5	2.1	/	4.8	9
0048001	0.5	2.1		4.8	9
0048002	0.5	2.1		4.8	9
0048003	0.5	2.1		4.8	9
0048005	0.5	2.1		4.8	9
0048006	0.5	2.1		4.8	9
0048007	0.5	2.1		4.8	9
0048008	0.5	2.1		4.8	9
0048009	0.5	2.1		4.8	9
0048104	0.5	2.1		4.8	9
0048105	0.5	2.1		4.8	9
0048106	0.5	2.1		4.8	9
0049000	0.75	2.4	/	7.2	12
0049001	0.75	2.4		7.2	12
0049002	0.75	2.4		7.2	12
0049003	0.75	2.4		7.2	12
0049005	0.75	2.4		7.2	12
0049006	0.75	2.4		7.2	12
0049007	0.75	2.4		7.2	12
0049008	0.75	2.4		7.2	12
0049009	0.75	2.4		7.2	12

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



ÖLFLEX® HEAT 180 SIF

	(mm ²)	(mm)		(kg/km)	(kg/km)
0049104	0.75	2.4		7.2	12
0049105	0.75	2.4		7.2	12
0049106	0.75	2.4		7.2	12
0050000	1.0	2.5	/	9.6	15
0050001	1.0	2.5		9.6	15
0050002	1.0	2.5		9.6	15
0050003	1.0	2.5		9.6	15
0050005	1.0	2.5		9.6	15
0050006	1.0	2.5		9.6	15
0050007	1.0	2.5		9.6	15
0050008	1.0	2.5		9.6	15
0050009	1.0	2.5		9.6	15
0050104	1.0	2.5		9.6	15
0050105	1.0	2.5		9.6	15
0050106	1.0	2.5		9.6	15
0051000	1.5	2.8	/	14.4	20
0051001	1.5	2.8		14.4	20
0051002	1.5	2.8		14.4	20
0051003	1.5	2.8		14.4	20
0051005	1.5	2.8		14.4	20
0051006	1.5	2.8		14.4	20
0051007	1.5	2.8		14.4	20
0051008	1.5	2.8		14.4	20
0051009	1.5	2.8		14.4	20
0051104	1.5	2.8		14.4	20
0051105	1.5	2.8		14.4	20
0051106	1.5	2.8		14.4	20
0052000	2.5	3.4	/	24	32
0052001	2.5	3.4		24	32
0052002	2.5	3.4		24	32
0052003	2.5	3.4		24	32
0052005	2.5	3.4		24	32
0052006	2.5	3.4		24	32
0052007	2.5	3.4		24	32

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 180 SIF

	(mm ²)	(mm)		(kg/km)	(kg/km)
0052104	2.5	3.4		24	32
0052105	2.5	3.4		24	32
0052106	2.5	3.4		24	32
0053000	4.0	4.2	/	38	50
0053001	4.0	4.2		38	50
0053002	4.0	4.2		38	50
0053003	4.0	4.2		38	50
0053005	4.0	4.2		38	50
0053006	4.0	4.2		38	50
0053009	4.0	4.2		38	50
0053104	4.0	4.2		38	50
0053105	4.0	4.2		38	50
0053106	4.0	4.2		38	50
0054000	6.0	5	/	58	73
0054001	6.0	5		58	73
0054002	6.0	5		58	73
0054003	6.0	5		58	73
0054005	6.0	5		58	73
0054006	6.0	5		58	73
0054104	6.0	5		58	73
0054105	6.0	5		58	73
0054106	6.0	5		58	73
0055000	10.0	6.6	/	96	118
0055001	10.0	6.6		96	118
0055002	10.0	6.6		96	118
0055003	10.0	6.6		96	118
0055009	10.0	6.6		96	118
0055104	10.0	6.6		96	118
0055105	10.0	6.6		96	118
0055106	10.0	6.6		96	118
0056000	16.0	7.4	/	154	177
0056001	16.0	7.4		154	177
0056002	16.0	7.4		154	177
0056104	16.0	7.4		154	177

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 180 SIF

	(mm ²)	(mm)		(kg/km)	(kg/km)
0056105	16.0	7.4		154	177
0056106	16.0	7.4		154	177
0057000	25.0	9.2	/	240	277
0057001	25.0	9.2		240	277
0057002	25.0	9.2		240	277
0057104	25.0	9.2		240	277
0057106	25.0	9.2		240	277
0058000	35.0	10.3	/	336	374
0058001	35.0	10.3		336	374
0058002	35.0	10.3		336	374
0058104	35.0	10.3		336	374
0059000	50.0	12.2	/	480	530
0059001	50.0	12.2		480	530
0059104	50.0	12.2		480	530
0060001	70.0	14.2		672	724
0060002	70.0	14.2		672	724
0061000	95.0	16.6	/	912	982
0061001	95.0	16.6		912	982
0061105	95.0	16.6		912	982
0062000	120.0	18	/	1152	1219
0062001	120.0	18		1152	1219
0063001	150.0	20		1440	1524
0064001	185.0	22.5		1776	1915

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16