

ÖLFLEX® HEAT 180 GLS

가

ÖLFLEX® HEAT 180 GLS - +180°C ,



SiO₂() 가

가 가

-
-
-
-
-

(23.12.2023)

ÖLFLEX® HEAT 180 GLS

(IEC 60754-1), 가 (IEC 60754-2), (IEC 60332-1-2)
 가 +100°C 가

-
 - ,
 -

ETIM 5: ETIM 5.0 Class-ID: EC001578
 ETIM 5.0 Class 가
 ETIM 6: ETIM 6.0 Class-ID: EC001578
 ETIM 6.0 Class :
 : VDE 0293-308 , T9
 6 :
 : VDE 0295 5/ IEC 60228 5
 가 가
 : : 20 x
 : 4 x
 : U0/U: 300/500 V
 : 2000 V
 : G = GN/YE
 X = GN/YE
 : -50 °C +180 °C
 ()

, 가 가 (.) 가 .
 : www.lappkabel.de/en/cable-standradlengths
 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

ÖLFLEX® HEAT 180 GLS

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 GLS				
0046201	2 X 0.75	7.6	14.4	84
0046202	3 G 0.75	8	21.6	96
00462033	4 G 0.75	8.8	28.8	118
00462043	5 G 0.75	9.7	36	145
0046205	6 G 0.75	10.4	43.2	167
0046206	7 G 0.75	10.4	50.4	171
0046207	2 X 1.0	7.8	19.2	92
0046208	3 G 1.0	8.2	28.8	106
00462093	4 G 1.0	9.1	38.4	132
00462103	5 G 1.0	10	48	161
0046212	7 G 1.0	10.7	67	205
0046213	2 X 1.5	8.8	29	119
0046214	3 G 1.5	9.2	43	140
00462153	4 G 1.5	10	57.6	168
00462163	5 G 1.5	10.8	72	212
0046218	7 G 1.5	11.8	101	255
0046237	12 G 1.5	15.4	173	433
0046219	2 X 2.5	10	48	162
0046220	3 G 2.5	10.9	72	217
00462213	4 G 2.5	12	96	260
00462223	5 G 2.5	13	120	310
0046224	7 G 2.5	14	168	362
0046226	3 G 4.0	12.9	115	300
00462273	4 G 4.0	14	154	365
00462283	5 G 4.0	15.4	192	446
00462313	4 G 6.0	16.1	230	500
00462343	4 G 10.0	20.8	384	807
00462353	4 G 16.0	22.8	614	1117

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16