

# ÖLFLEX® 409 P

가


PUR

-

ÖLFLEX® 409 P - PUR UL/cUL

UL/cUL

가



PUR

,

가

가

( )

,

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® 409 P

UL/CSA: VW-1, FT1.  
IEC/EN: 60332-1-2

ISO 4892-2 UV-  
가

UL File No. E63634  
UL AWM Style 20234  
cUL AWM I/II A/B FT1

: PVC

: (RAL 9005 )

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

: Black with white numbers acc. to VDE 0293-334

: IEC 60228/VDE 0295 class 5

: : 12.5 x

: 4 x

: U0/U: 300/500 V

UL/CSA: 1000 V

: 4000 V

: G = GN/YE

X = GN/YE

: : -5°C ~ +70°C (UL: +80°C)

: -40°C +80°C

, 가 가 . ( . ) 가 .  
: [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1311852	2 X 0.75	6.7	14.4	61
1311103	3 G 0.75	7.0	21.6	71
1311104	4 G 0.75	7.5	28.8	84
1311105	5 G 0.75	8.1	36	100
1311107	7 G 0.75	8.7	50.4	122
1311110	10 G 0.75	10.6	72	180
1311112	12 G 0.75	10.9	86.4	198
1311118	18 G 0.75	12.6	129.6	275
1311125	25 G 0.75	14.3	180	364
1311902	2 X 1.0	7.0	19.2	69
1311203	3 G 1.0	7.3	28.8	81
1311204	4 G 1.0	7.8	38.4	97
1311205	5 G 1.0	8.5	48	117
1311207	7 G 1.0	9.0	67.2	142
1311210	10 G 1.0	11.2	96	212
1311212	12 G 1.0	11.5	115.2	234
1311218	18 G 1.0	13.3	172.8	327
1311225	25 G 1.0	15.2	240	437
1311952	2 X 1.5	7.6	28.8	87
1311303	3 G 1.5	8.0	43.2	104
1311304	4 G 1.5	8.6	57.6	126
1311305	5 G 1.5	9.3	72	151
1311307	7 G 1.5	10.0	100.8	188
1311312	12 G 1.5	12.8	172.8	314
1311318	18 G 1.5	14.8	259.2	441
1311325	25 G 1.5	17.2	360	596
1311403	3 G 2.5	9.3	72	151
1311404	4 G 2.5	10.0	96	184
1311405	5 G 2.5	10.9	120	224
1311407	7 G 2.5	11.8	168	282
1311412	12 G 2.5	15.3	288	480
1311504	4 G 4.0	11.6	153.6	266
1311505	5 G 4.0	12.7	192	325
1311604	4 G 6.0	13.4	230.4	359

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® 409 P

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1311605	5 G 6.0	14.7	288	438
1311704	4 G 10.0	17.0	384	585
1311705	5 G 10.0	18.7	480	722
1311804	4 G 16.0	19.6	614.4	861
1311805	5 G 16.0	22.2	768	1107

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16