

ÖLFLEX® HEAT 180 H05SS-F EWKF

가

ÖLFLEX® HEAT 180 H05SS-F EWKF - +180°C

H05SS-F

EWKF



H05SS-F

SiO2()

가

가 가

- ,
-
-

(23.04.2024)

ÖLFLEX® HEAT 180 H05SS-F EWKF

- /
- 가
-
-
-
-

EWKF:

가 (IEC 60754-1), UV- 가 (IEC 60754-2), (IEC 60332-1-2)
 가 , , , +100°C 가

EN 50525-2-83 (H05SS-F)

: EWKF

: EWKF, ,

ETIM 5:

ETIM 5.0 Class-ID: EC001578
 ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578
 ETIM 6.0 Class :

:

VDE 0293-308 , T9

:

VDE 0295 5/ IEC 60228 5
 가 가

:

: 15 x
 : 4 x

:

U0/U: 300/500 V

:

2000 V

:

G = GN/YE

X = GN/YE

:

-50 °C +180 °C
 ()

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)



ÖLFLEX® HEAT 180 H05SS-F EWKF

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 H05SS-F EWKF				
0046900	2 X 0.75	6.4	14.4	54
0046901	3 G 0.75	7	21.6	67
00469023	4 G 0.75	7.6	28.8	87
00469033	5 G 0.75	8.5	36	105
0046904	2 X 1.0	6.8	19.2	63
0046905	3 G 1.0	7.2	28.8	81
00469063	4 G 1.0	7.9	38.4	98
00469073	5 G 1.0	8.8	48	121
0046908	2 X 1.5	8.4	28.8	84
0046909	3 G 1.5	8.9	43.2	103
00469103	4 G 1.5	9.9	57.6	128
00469113	5 G 1.5	10.9	72	154
0046912	2 X 2.5	9.8	48	141
0046913	3 G 2.5	10.4	72	158
00469143	4 G 2.5	11.6	96	195
00469153	5 G 2.5	12.9	120	241
0046916	3 G 4.0	12.3	115.2	239
00469173	4 G 4.0	13.7	153.6	312
0046919	3 G 6.0	14	172.8	345
00469203	4 G 6.0	15.6	230.4	451

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16