

ÖLFLEX® HEAT 180 FZLSi

ÖLFLEX® HEAT 180 FZLSi - +180°C

10 kV

10 kV



SiO₂() 가

-
- 가

- /

-

-

-

-

-

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 FZLSi

IEC 60754-1

(가)

IEC 60754-2 (가) , 가

: IEC 60332-1-2

가

+100°C

가

2006/95/EC

가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

VDE 0295, Class 5 / IEC 60228 Class 5 가
(0.5mm²)

:

: 6 x

1 , :

3 x

:

Version SiF/GL / SiZ:

U0/U 300/500 V

Version FZLSi:

10 kV

:

SiF/GL / SiZ:

2000V

FZLSi:

20kV

:

-50 °C +180 °C

()

: +200°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT

가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 180 FZLSi

	(mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 FZLSi				
2510001	1 (32 x 0,2)	7	9.6	68
2510005	1.5 (30 x 0,25)	7.6	14.4	83

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16