

ÖLFLEX® HEAT 180 SiD

가

ÖLFLEX® HEAT 180 SiD - +180°C



SiO2() 가

-
-가

- /

-
-
-
-
-
-
-

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 SiD

IEC 60754-1

(가)

IEC 60754-2 () , 가

: IEC 60332-1-2

가

+100°C

가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

:

: 6 x

1 , :

3 x

:

U0/U: 300/500 V

:

2000 V

:

-50 °C +180 °C

()

: +200°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

가 가

가 VAT

가 가

가

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 180 SiD

	(mm ²)	(mm)		(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 SiD					
0068001	0.5	2		4.8	9
0068105	0.5	2		4.8	9
0069000	0.75	2.2	/	7.2	12
0069001	0.75	2.2		7.2	12
0069002	0.75	2.2		7.2	12
0069003	0.75	2.2		7.2	12
0069105	0.75	2.2		7.2	12
0070000	1.0	2.3	/	9.6	15
0070001	1.0	2.3		9.6	15
0070002	1.0	2.3		9.6	15
0070003	1.0	2.3		9.6	15
0070104	1.0	2.3		9.6	15
0070105	1.0	2.3		9.6	15
0071000	1.5	2.6	/	14.4	20
0071001	1.5	2.6		14.4	20
0071002	1.5	2.6		14.4	20
0071003	1.5	2.6		14.4	20
0071105	1.5	2.6		14.4	20
0072001	2.5	3.2		24	32
0072002	2.5	3.2		24	32
0073001	4.0	3.9		38	50
0074001	6.0	4.6		58	64.5
0074002	6.0	4.6		58	64.5

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16