

# ÖLFLEX® HEAT 180 SiF/GL

ÖLFLEX® HEAT 180 SiF/GL - +180°C ,



SiO2( ) 가

-  
- 가

- /

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

ÖLFLEX®HEAT 180 SiZ

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® HEAT 180 SiF/GL

IEC 60754-1

( 가 )

IEC 60754-2 ( ) , 가

: IEC 60332-1-2

가

+100°C

가

가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

:

VDE 0295, Class 5 / IEC 60228 Class 5 가  
(0.5mm<sup>2</sup> )

:

: 6 x

1 , :  
3 x

:

Version SiF/GL / SiZ:

U0/U 300/500 V

Version FZLSi:

10 kV

:

SiF/GL / SiZ:

2000V

FZLSi:

20kV

:

-50 °C +180 °C

( )

: +200°C

, 가 가 . ( . ) 가 .

[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT

가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® HEAT 180 SiF/GL

	(mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 SiF/GL	가			
0065102	0.5	2.5	4.8	11
0065103	0.75	2.8	7.2	14
0065104	1.0	2.9	9.6	17
0065105	1.5	3.2	14.4	23
0065106	2.5	3.8	24	36
0065107	4.0	4.6	38	54
0065108	6.0	5.4	58	80
0065109	10.0	7.6	96	133
0065110	16.0	8.4	154	198
0065111	25.0	10.2	240	301
0065112	35.0	11.3	336	401
0065113	50.0	13.4	480	567

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16