

ÖLFLEX® ROBUST 200

ÖLFLEX® ROBUST 200 -

Good chemical resistance please see Appendix T1
450/750 V



가 , , UV

가 , ,

(24.04.2024)

ÖLFLEX® ROBUST 200

EN 50396 HD 605 S2 /UV /
 , -40°C

5

EN 50525-2-51

EN50565-2 +40 °C 10m 가

PP

TPE
 :

ETIM 5: ETIM 5.0 Class-ID: EC001578
 ETIM 5.0 Class 가

ETIM 6: ETIM 6.0 Class-ID: EC001578
 ETIM 6.0 Class :

: 5 : VDE 0293-308 T9
 6 :

: IEC 60228/VDE 0295 class 5

: : 10 x
 : 4 x

: U0/U: 450/750 V

: 4000 V

: G = GN/YE

: X = GN/YE

: : -40°C ~ +80°C
 : -50°C +80°C

가 가 (.) 가 .

: www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

: 4G16 600 m; 4G25 300 m; 4G50 250 m

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® ROBUST 200

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® ROBUST 200

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® ROBUST 200				
0021800	2 X 1.0	8	19.2	65
0021801	3 G 1.0	8.4	29	79
0021802	4 G 1.0	9.2	38.4	96
0021803	5 G 1.0	10	48	113
0021805	2 X 1.5	8.6	29	78
0021806	3 G 1.5	9.1	43	97
0021807	4 G 1.5	9.9	58	122
0021808	5 G 1.5	10.8	72	146
0021809	7 G 1.5	13.5	101	208
0021810	2 X 2.5	9.8	48	114
0021811	3 G 2.5	10.4	72	144
0021812	4 G 2.5	11.5	96	181
0021813	5 G 2.5	13.1	120	222
0021814	7 G 2.5	15.9	168	312
0021816	3 G 4.0	12.4	115.2	215
0021817	4 G 4.0	14	154	273
0021818	5 G 4.0	15.8	192	333
0021822	4 G 6.0	15.7	230	378
0021823	5 G 6.0	17.2	288	463
0021825	4 G 10.0	19.4	384	570
0021826	5 G 10.0	21.4	480	770
0021828	4 G 16.0	22.4	614	885
0021829	5 G 16.0	24.6	768	1100
0021831	4 G 25.0	27	960	1365
0021833	4 G 35.0	29.7	1344	1773
0021836	4 G 50.0	36.2	1920	3454

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16