

ÖLFLEX® HEAT 180 SiZ

ÖLFLEX® HEAT 180 SiZ - +180°C

가



SiO2() 가

-
- 가

- /

ÖLFLEX®HEAT 180 SiZ

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 SiZ

IEC 60754-1

(가)

IEC 60754-2 () , 가

: IEC 60332-1-2

가 , , +100°C 가

가 가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class :

: VDE 0295, Class 5 / IEC 60228 Class 5 가
(0.5mm²)

: : 6 x

1 , :

3 x

: Version SiF/GL / SiZ:

U0/U 300/500 V

Version FZLSi:

10 kV

: SiF/GL / SiZ:

2000V

FZLSi:

20kV

: -50 °C +180 °C

()

: +200°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® HEAT 180 SiZ

	(mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® HEAT 180 SiZ				
0065201	2 x 0.5	2.1 x 4.2	9.6	17
0065202	2 x 0.75	2.3 x 4.6	14.4	24

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16