

H07RN8-F

, : "ÖLFLEX® AQUA RN8"

H07RN8-F, HAR, , , 450/750V, 10m , , class 5, ,

10m



EN 50565-2 , EN 50565-2

가 <HAR> - CENELEC 가 "<HAR>"

(25.04.2024)

H07RN8-F

EN 50565-2 : 가 ,

AD8 10m

: IEC 60332-1-2
EN 60811-404

EN 50525-2-21 <HAR>

: EI 4
: , type EM2

ETIM 5:

ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

: 5 : VDE 0293-308 . T9
6 :

: VDE 0295 5/ IEC 60228 5
가 가

: 4 ~ 8 x (EN 50565-1)

: U0/U: 450/750 V

: 2500 V

: G = GN/YE

: X = GN/YE

: VDE 0298 4
EN 50565-1/ VDE 0298-565-1

: Fixed installation: -40 up to +60°C
Occasionally moved: -25°C up to +60°C
: +40°C

: 30 kg, 가 가 (.) 가 .
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(25.04.2024)

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1600600	1 X 4.0	7.2 - 7.8	38.4	100
1600601	1 X 6.0	7.9 - 8.5	57.6	120
1600602	1 X 10.0	9.5 - 10.5	96	180
1600604	1 X 25.0	12.7 - 13.7	240	400
1600606	3 G 1.5	9.2 - 10.8	43.2	141
1600609	4 G 1.5	10.2 - 11.8	57.6	205
1600620	7 G 1.5	14 - 17.5	100.8	385
1600607	3 G 2.5	10.9 - 12.5	72	210
1600610	4 G 2.5	12.1 - 13.9	96	260
1600621	7 G 2.5	16.5 - 20	168	520
1600611	4 G 4.0	14.0 - 16.0	153.6	356
1600612	4 G 6.0	15.7 - 17.7	230.4	475
1600613	4 G 10.0	20.9 - 23.3	384	837
1600614	4 G 16.0	23.8 - 26.4	614.4	1220
1600615	4 G 25.0	28.9 - 32.1	960	1770
1600616	4 G 35.0	32.5 - 36.1	1344	2304

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16