

ÖLFLEX® SERVO Basic Line according to Siemens 6FX5002 (PVC)

PVC



Lapp



가

Lapp

(25.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® SERVO Basic Line according to Siemens 6FX5002 (PVC)

가

PVC ,
PVC

SIEMENS® 6FX 5002

IEC 60332-1-2, VW-1, FT1

1.5mm² 가

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

:

: U/L1/C/L+ ; V/L2; W/L3/D/L-;

GN/YE

:

2 : ; 5; 6; 7; 8

0,34mm² : / / /

:

IEC 60228/VDE 0295 class 5

:

: 15 x

: 6 x

:

U0/U: 600/1000 V

UL & CSA: 1000 V

:

Core/Core: 4 kV

Core/Screen: 4 kV

:

G = GN/YE

:

: -5°C ~ +70°C (UL: +80°C)

: -30°C +80°C

Siemens

가 가 () 가
(6FX5002/5008, 6FX7002/7008, 6FX8002/8008) Siemens AG

가

(25.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO Basic Line according to Siemens 6FX5002 (PVC)

가 VAT 가 가 .

Further Article and length online <https://servoconfigurator.lappgroup.com/>

(25.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO Basic Line according to Siemens 6FX5002 (PVC)

	(mm)	(m)	(CORE) / (mm ²)	SIEMENS®	kg/1.000 pieces		PU
5480003015	9.6	10.0	4G2,5	5CN11	1353	가	1
5480004290	10.4	10.0	4 G 1,5+(2x1,5)	5DQ28	1,686.7	가	1
5480004515	12	10.0	4 G 2,5+(2x1,5)	5DS31	1,988.5	가	1

(25.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16