

ÖLFLEX® 440 P

TPE PUR - VDE

ÖLFLEX® 440 P - PUR - , , , VDE

VDE



PUR

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® 440 P

VDE

IEC 61892-4, D (MUD)
(IEC 60332-1-2)
가
, -40°C

VDE 6582
EN50565-2 +40 °C 10m 가

: TPE

: (PUR)
(RAL 7001)

ETIM 5: ETIM 5.0 Class-ID: EC000104
ETIM 5.0
ETIM 6: ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :
: Black with white numbers acc. to VDE 0293-334
: IEC 60228/VDE 0295 class 5
: : 12.5 x
: 4 x
: U0/U: 300/500 V
: 3000 V
: G = GN/YE
X = GN/YE
: : -40°C ~ +90°C
: -50°C +90°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,

(24.04.2024)



ÖLFLEX® 440 P

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® 440 P

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® 440 P				
0012800	2 X 0.5	5.8	10	39
0012801	3 G 0.5	6.1	14	46
0012802	4 G 0.5	6.6	19	53
0012803	5 G 0.5	7.3	24	65
0012804	7 G 0.5	8.8	34	92
0012805	12 G 0.5	10.9	58	149
0012806	18 G 0.5	12.9	86	207
0012807	25 G 0.5	15.7	120	274
0012813	2 X 0.75	6.2	14	48
0012814	3 G 0.75	6.5	22	53
0012815	4 G 0.75	7.1	29	67
0012816	5 G 0.75	8	36	81
0012817	7 G 0.75	9.7	50	119
0012818	12 G 0.75	11.7	86	193
0012819	18 G 0.75	14.1	130	269
0012820	25 G 0.75	17.1	180	378
0012825	2 X 1.0	6.5	19	57
0012826	3 G 1.0	6.9	29	61
0012827	4 G 1.0	7.7	38	82
0012828	5 G 1.0	8.4	48	107
0012829	7 G 1.0	10.2	67	138
0012830	12 G 1.0	12.6	115	215
0012831	18 G 1.0	14.9	173	328
0012832	25 G 1.0	18.1	240	479
0012833	34 G 1.0	20.6	326	616
0012834	41 G 1.0	22.4	394	727
0012837	2 X 1.5	7.1	29	73
0012838	3 G 1.5	7.5	43	96
0012839	4 G 1.5	8.4	58	105
0012840	5 G 1.5	9.4	72	133
0012841	7 G 1.5	11.4	101	175
0012842	12 G 1.5	14	173	309
0012843	18 G 1.5	16.6	259	458

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



ÖLFLEX® 440 P

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
0012844	25 G 1.5	20.1	360	635
0012846	41 G 1.5	25.1	590	1003
0012850	3 G 2.5	9.2	72	142
0012851	4 G 2.5	10	96	184
0012852	5 G 2.5	11.2	120	220
0012853	7 G 2.5	13.8	168	294
0012854	12 G 2.5	16.9	288	489

(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16