



ÖLFLEX® 500 P

PUR

ÖLFLEX® 500 P -

가

PUR

가



PUR

가

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® 500 P

가 , 가 가

IEC 61892-4, D (MUD)

, -40°C

(IEC 60332-1-2)

가

VDE 0285
EN50565-2

+40 °C

10m

가

: TPE

PUR

:

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

:

VDE 0293-308 , T9

:

VDE 0295, 6/ IEC 60228 6

:

: 10 x

: 4 x

:

U0/U: 300/500 V

:

3000 V

:

G = GN/YE

X = GN/YE

:

: -40°C ~ +80°C

: -50°C +80°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® 500 P

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® 500 P				
0012345	2 X 1.0	6.8	19.5	64
0012346	3 G 1.0	7.2	29	77
00123473	4 G 1.0	8.1	38.4	96
00123483	5 G 1.0	8.9	48	120
0012351	2 X 1.5	7.6	29	81
0012352	3 G 1.5	8.3	43	105.3
00123543	4 G 1.5	9.3	58	135
00123533	5 G 1.5	10.4	72	158.9
0012365	3 G 2.5	10.4	72	173.2
00123553	4 G 2.5	11.4	96	204
00123663	5 G 2.5	12.8	120	254