



# ÖLFLEX® SPIRAL 400 P

가 가 PUR

ÖLFLEX® SPIRAL 400 P - PUR

T1

Available in cross sections starting at 0,5 mm<sup>2</sup>



PUR

3

,가

T1

(16.05.2025)

©2025 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® SPIRAL 400 P

Norm references / Approvals

VDE 0812/0285

VDE 0250/0285

가  
 : PVC P8/1  
 : = 200 mm, = 600 mm (VDE )  
 가 LAPP , ,

ETIM 5: ETIM 5.0 Class-ID: EC000247  
 ETIM 5.0 Class :  
 ETIM 6: ETIM 6.0 Class-ID: EC000247  
 ETIM 6.0 Class-Description: Spiralized cable  
 : Black with white numbers acc. to VDE 0293-334  
 : VDE 0295 5/ IEC 60228 5  
 가 가  
 : U0/U: 300/500 V  
 : 3000 V  
 : G = GN/YE  
 : X = GN/YE  
 : : +5°C +50°C

가 VAT 가 가 . ( . ) 가 .  
 가 LAPP , , (VDE )  
 가

(16.05.2025)

©2025 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® SPIRAL 400 P

	(CORE) / (mm <sup>2</sup> )	(mm)	(mm)	(mm)	(mm)
70002598	2 X 0.5	1500	500	5.5	20
70002599	2 X 0.5	3000	1000	5.5	20
70002600	2 X 0.5	4500	1500	5.5	20
70002601	2 X 0.5	6000	2000	5.5	20
70002602	3 G 0.5	1500	500	5.8	21
70002603	3 G 0.5	3000	1000	5.8	21
70002604	3 G 0.5	4500	1500	5.8	21
70002605	3 G 0.5	6000	2000	5.8	21
70002606	4 G 0.5	1500	500	6.2	21
70002607	4 G 0.5	3000	1000	6.2	21
70002608	4 G 0.5	4500	1500	6.2	21
70002609	4 G 0.5	6000	2000	6.2	21
70002610	5 G 0.5	1500	500	6.7	25
70002611	5 G 0.5	3000	1000	6.7	25
70002612	5 G 0.5	4500	1500	6.7	25
70002613	5 G 0.5	6000	2000	6.7	25
70002614	7 G 0.5	1500	500	7.6	29
70002615	7 G 0.5	3000	1000	7.6	29
70002616	7 G 0.5	4500	1500	7.6	29
70002617	7 G 0.5	6000	2000	7.6	29
70002618	12 G 0.5	1500	500	9.5	32
70002619	12 G 0.5	3000	1000	9.5	32
70002620	18 G 0.5	1500	500	11	42
70002621	18 G 0.5	3000	1000	11	42
70002622	2 X 0.75	1500	500	5.6	19.5
70002623	2 X 0.75	3000	1000	5.6	19.5
70002624	2 X 0.75	4500	1500	5.6	19.5
70002625	2 X 0.75	6000	2000	5.6	19.5
70002628	3 G 0.75	1500	500	5.9	20
70002629	3 G 0.75	3000	1000	5.9	20
70002630	3 G 0.75	4500	1500	5.9	20
70002631	3 G 0.75	6000	2000	5.9	20
70002634	4 G 0.75	1500	500	6.4	21
70002635	4 G 0.75	3000	1000	6.4	21

(16.05.2025)

©2025 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® SPIRAL 400 P

	(CORE) /	(mm <sup>2</sup> )	(mm)	(mm)	(mm)	(mm)
70002636	4 G 0.75	4500	1500	6.4	21	
70002637	4 G 0.75	6000	2000	6.4	21	
70002640	5 G 0.75	1500	500	6.9	24	
70002641	5 G 0.75	3000	1000	6.9	24	
70002642	5 G 0.75	4500	1500	6.9	24	
70002643	5 G 0.75	6000	2000	6.9	24	
70002726	7 G 0.75	1500	500	7.5	27	
70002727	7 G 0.75	3000	1000	7.5	27	
70002728	7 G 0.75	4500	1500	7.5	27	
70002729	7 G 0.75	6000	2000	7.5	27	
70002731	12 G 0.75	1500	500	9.9	35	
70002732	12 G 0.75	3000	1000	9.9	35	
70002734	18 G 0.75	1500	500	11.9	40	
70002735	18 G 0.75	3000	1000	11.9	40	
70002646	2 X 1.0	1500	500	5.9	20	
70002647	2 X 1.0	3000	1000	5.9	20	
70002648	2 X 1.0	4500	1500	5.9	20	
70002649	2 X 1.0	6000	2000	5.9	20	
70002651	3 G 1.0	1500	500	6.2	21	
70002652	3 G 1.0	3000	1000	6.2	21	
70002653	3 G 1.0	4500	1500	6.2	21	
70002654	3 G 1.0	6000	2000	6.2	21	
70002656	4 G 1.0	1500	500	6.7	24	
70002657	4 G 1.0	3000	1000	6.7	24	
70002658	4 G 1.0	4500	1500	6.7	24	
70002659	4 G 1.0	6000	2000	6.7	24	
70002661	5 G 1.0	1500	500	7.3	25	
70002662	5 G 1.0	3000	1000	7.3	25	
70002663	5 G 1.0	4500	1500	7.3	25	
70002664	5 G 1.0	6000	2000	7.3	25	
70002666	7 G 1.0	1250	500	8.2	30	
70002667	7 G 1.0	2500	1000	8.2	30	
70002668	7 G 1.0	3750	1500	8.2	30	
70002669	7 G 1.0	5000	2000	8.2	30	

(16.05.2025)

©2025 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® SPIRAL 400 P

	(CORE) /	(mm <sup>2</sup> )	(mm)	(mm)	(mm)	(mm)
70002670	12 G 1.0	1500	500	10.9	37	
70002671	12 G 1.0	3000	1000	10.9	37	
70002672	18 G 1.0	1500	500	12.7	45	
70002673	18 G 1.0	3000	1000	12.7	45	
70002681	2 X 1.5	1500	500	6.5	23	
70002682	2 X 1.5	3000	1000	6.5	23	
70002683	2 X 1.5	4500	1500	6.5	23	
70002684	2 X 1.5	6000	2000	6.5	23	
70002687	3 G 1.5	1500	500	6.9	24	
70002688	3 G 1.5	3000	1000	6.9	24	
70002689	3 G 1.5	4500	1500	6.9	24	
70002690	3 G 1.5	6000	2000	6.9	24	
70002699	5 G 1.5	1250	500	8.3	30	
70002700	5 G 1.5	2500	1000	8.3	30	
70002701	5 G 1.5	3750	1500	8.3	30	
70002702	5 G 1.5	5000	2000	8.3	30	
70002705	7 G 1.5	1250	500	9.1	31	
70002706	7 G 1.5	2500	1000	9.1	31	
70002707	7 G 1.5	3750	1500	9.1	31	
70002708	7 G 1.5	5000	2000	9.1	31	
70002709	12 G 1.5	1500	500	12.2	46	
70002710	12 G 1.5	3000	1000	12.2	46	
70002711	18 G 1.5	1500	500	14.2	52	
70002712	18 G 1.5	3000	1000	14.2	52	
70002716	3 G 2.5	1250	500	8.3	28.5	
70002717	3 G 2.5	2500	1000	8.3	28.5	
70002718	3 G 2.5	3750	1500	8.3	28.5	
70002719	3 G 2.5	5000	2000	8.3	28.5	
70002721	5 G 2.5	1250	500	10	37	
70002722	5 G 2.5	2500	1000	10	37	
70002723	5 G 2.5	3750	1500	10	37	
70002724	5 G 2.5	5000	2000	10	37	

(16.05.2025)

©2025 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16