

ÖLFLEX® 540 CP

ÖLFLEX® 540 CP - PUR - VDE

1.5 mm² 450/750 V

VDE



(23.04.2024)

ÖLFLEX® 540 CP

PUR

VDE

가

IEC 61892-4, D (MUD)

(IEC 60332-1-2)

, -40°C

EMC-

VDE 6583 1.0mm²

VDE 6584 1.5mm²

EN50565-2 +40 °C 10m 가

: TPE

TPE

: PUR –

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

:

VDE 0293-308 , T9

(7 ,)

:

IEC 60228/VDE 0295 class 5

:

: 12.5 x

: 6 x

:

1.0 mm²: U0/U: 300/500 V

.5 mm² : U0/U: 450/750 V

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® 540 CP

: 3000 V
 : G = GN/YE
 : X = GN/YE
 : : -40°C ~ +90°C
 : -50°C +90°C

, 가 가 . (.) 가 .
 : www.lappkabel.de/en/cable-standradlengths
 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® 540 CP U0/U: 300/500 V				
0012752	2 X 0.75	8.2	43.9	103
0012753	3 G 0.75	8.5	67.6	140
00127553	5 G 0.75	10.2	75	164
0012757	2 X 1.0	8.5	65.2	138
0012758	3 G 1.0	9.3	74.9	153
00127603	5 G 1.0	10.8	87.2	184
0012761	7 G 1.0	12.6	138.5	281
ÖLFLEX® 540 CP U0/U: 450/750 V				
0012762	2 X 1.5	10.5	67.7	159
0012763	3 G 1.5	11	82.3	181
00127643	4 G 1.5	12	101.8	218
00127653	5 G 1.5	13.7	143.3	287
0012766	7 G 1.5	16.6	195.7	394
0012767	2 X 2.5	11.9	92.4	213
0012768	3 G 2.5	12.5	119	263
00127693	4 G 2.5	14.2	168.2	334
00127703	5 G 2.5	15.7	204.7	416
00127753	4 G 4.0	17	240.1	476
00127783	4 G 6.0	18.4	355.5	634
00127793	5 G 6.0	20.5	452.9	770
00127813	4 G 10.0	22.3	577.8	993
00127823	5 G 10.0	25.3	681.2	1151

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16