

# ÖLFLEX® 540 P

TPE/PUR - VDE

ÖLFLEX® 540 P - PUR , VDE

1.5 mm<sup>2</sup> 450/750 V

VDE



PUR

(25.04.2024)

# ÖLFLEX® 540 P

VDE 가

IEC 61892-4, D (MUD)  
(IEC 60332-1-2)  
, -40°C  
가

VDE 6583 1.0mm<sup>2</sup>

VDE 6584 1.5mm<sup>2</sup>

EN50565-2 +40 °C 10m 가

: TPE

: PUR –

가

PRINT:

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

:

VDE 0293-308 , T9  
(7 , )

:

IEC 60228/VDE 0295 class 5

:

: 10 x

:

1.0 mm<sup>2</sup>: U0/U: 300/500 V

:

3000 V

:

G = GN/YE

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® 540 P

X = GN/YE

:

: -40°C ~ +90°C

: -50°C

+90°C

가 가 . ( . ) 가 .  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(25.04.2024)



# ÖLFLEX® 540 P

| Article number                | (CORE) / (mm <sup>2</sup> ) | (mm) | (kg/km) | (kg/km) |
|-------------------------------|-----------------------------|------|---------|---------|
| ÖLFLEX® 540 P U0/U: 300/500 V |                             |      |         |         |
| 0012452                       | 2 X 0.75                    | 6.2  | 14.4    | 52      |
| 0012453                       | 3 G 0.75                    | 6.7  | 21.6    | 63      |
| 00124543                      | 4 G 0.75                    | 7.3  | 28.8    | 80      |
| 00124553                      | 5 G 0.75                    | 8.2  | 36      | 98      |
| 0012456                       | 7 G 0.75                    | 9.9  | 51      | 126     |
| 0012457                       | 2 X 1.0                     | 6.7  | 19.2    | 53      |
| 0012458                       | 3 G 1.0                     | 7.1  | 29      | 72      |
| 00124593                      | 4 G 1.0                     | 7.7  | 38.4    | 96      |
| 00124603                      | 5 G 1.0                     | 8.6  | 48      | 117     |
| 0012461                       | 7 G 1.0                     | 10.4 | 68      | 147     |
| ÖLFLEX® 540 P U0/U: 450/750 V |                             |      |         |         |
| 0012462                       | 2 X 1.5                     | 8.3  | 29      | 82      |
| 0012463                       | 3 G 1.5                     | 8.8  | 43      | 108     |
| 00124643                      | 4 G 1.5                     | 9.8  | 58      | 147     |
| 00124653                      | 5 G 1.5                     | 10.7 | 72      | 164     |
| 0012466                       | 7 G 1.5                     | 13.4 | 101     | 267     |
| 0012467                       | 2 X 2.5                     | 9.7  | 48      | 142     |
| 0012468                       | 3 G 2.5                     | 10.3 | 72      | 161     |
| 00124693                      | 4 G 2.5                     | 11.4 | 96      | 220     |
| 00124703                      | 5 G 2.5                     | 12.7 | 120     | 245     |
| 0012471                       | 7 G 2.5                     | 15.8 | 168     | 321     |
| 0012474                       | 3 G 4.0                     | 12.3 | 115.2   | 262     |
| 00124753                      | 4 G 4.0                     | 13.6 | 154     | 284     |
| 00124763                      | 5 G 4.0                     | 15.2 | 192     | 355     |
| 00124783                      | 4 G 6.0                     | 15.4 | 230     | 440     |
| 00124793                      | 5 G 6.0                     | 17.1 | 288     | 530     |
| 00124813                      | 4 G 10.0                    | 20.1 | 384     | 615     |
| 00124823                      | 5 G 10.0                    | 22.3 | 480     | 735     |

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16