

# ÖLFLEX® CLASSIC 415 CP

PUR

ÖLFLEX® 415 CP - PUR

가

,

가 ,  
EMC



**CE UK EAC**  
**CA EAC**



PUR

,

,

,

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® CLASSIC 415 CP

EMC-

가

VDE 0812/0285  
VDE 0250/0285

: PVC

: (PUR)  
(RAL 7001)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	IEC 60228/VDE 0295 class 5
:	: 20 x
:	: 6 x
:	U0/U: 300/500 V
:	Core/core: 4000 V Core/screen: 2000 V
:	G = GN/YE X = GN/YE
:	: -5°C ~ +70°C : -40°C +80°C

가 가 ( ) 가  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가

# ÖLFLEX® CLASSIC 415 CP

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CLASSIC 415 CP				
1314000	2 X 0.5	5.8	36	45
1314001	3 G 0.5	6.1	43	59
1314002	3 X 0.5	6.1	43	59
1314003	4 G 0.5	6.5	49	83
1314004	4 X 0.5	6.5	49	83
1314005	5 G 0.5	7	57	96
1314006	5 X 0.5	7	57	96
1314007	7 G 0.5	7.5	69	136
1314008	7 X 0.5	7.5	69	136
1314010	12 G 0.5	9.9	104	200
1314011	12 X 0.5	9.9	104	200
1314012	18 G 0.5	11.5	141	275
1314013	18 X 0.5	11.5	141	275
1314014	25 G 0.5	13.4	211	350
1314015	25 X 0.5	13.4	211	350
1314017	2 X 0.75	6.2	43	56
1314018	3 G 0.75	6.5	52	70
1314019	3 X 0.75	6.5	52	70
1314020	4 G 0.75	7	61	95
1314021	4 X 0.75	7	61	95
1314022	5 G 0.75	7.7	72	130
1314023	5 X 0.75	7.7	72	130
1314024	7 G 0.75	8.3	89	168
1314025	7 X 0.75	8.3	89	168
1314026	12 G 0.75	10.9	138	232
1314027	18 G 0.75	12.7	211	315
1314028	25 G 0.75	14.8	280	435
1314029	25 X 0.75	14.8	280	435
1314032	2 X 1.0	6.5	51	84
1314033	3 G 1.0	6.8	62	110
1314034	3 X 1.0	6.8	62	110
1314035	4 G 1.0	7.3	74	130
1314036	4 X 1.0	7.3	74	130

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1314037	5 G 1.0	8.1	88	156
1314038	5 X 1.0	8.1	88	156
1314039	7 G 1.0	8.8	112	192
1314040	7 X 1.0	8.8	112	192
1314041	12 G 1.0	11.5	185	285
1314042	18 G 1.0	13.9	268	395
1314043	25 G 1.0	15.9	354	656
1314046	2 X 1.5	7.1	65	97
1314047	3 G 1.5	7.5	82	125
1314048	3 X 1.5	7.5	82	125
1314049	4 G 1.5	8.2	100	165
1314050	4 X 1.5	8.2	100	165
1314051	5 G 1.5	8.9	119	193
1314052	5 X 1.5	8.9	119	193
1314053	7 G 1.5	9.9	154	245
1314054	7 X 1.5	9.9	154	245
1314055	12 G 1.5	13	268	365
1314056	18 G 1.5	15.6	373	553
1314057	25 G 1.5	17.9	530	734
1314058	34 G 1.5	20.8	683	944
1314061	3 G 2.5	8.9	118	188
1314062	4 G 2.5	9.9	147	236
1314063	5 G 2.5	11	176	270
1314064	7 G 2.5	11.9	253	340
1314065	12 G 2.5	16	355	589
1314066	18 G 2.5	19	569	978
1314067	25 G 2.5	22.2	827	1358
1314068	4 G 4.0	11.6	248	305
1314070	7 G 4.0	14.4	355	500
1314071	4 G 6.0	14.2	343	440
1314073	7 G 6.0	17	505	672
1314074	4 G 10.0	17.2	535	710
1314075	4 G 16.0	20.2	800	1050
1314076	4 G 25.0	25.1	1075	1570

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® CLASSIC 415 CP

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1314077	4 G 35.0	28	1576	2070

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16